

FDT-CJ048NXV2000



iFDT Indoor Fiber Distribution Terminal, 48-fiber, SC/APC, loose tube IFC cable, 200 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Adapters, quantity	48
Cable Entry Location	Bottom right Top right
Cable Type	IFC - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/APC
Interface, stub	No connector
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	48

Dimensions

Height	476.25 mm 18.75 in
Width	368.3 mm 14.5 in
Depth	127 mm 5 in
Cable Length	60.96 m 200 ft

Ordering Tree

FDT-CJ048NXV2000



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1

FDT-CJ048NXV2000

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

