

# FDT-DJ072NXV2000

---



iFDT Indoor Fiber Distribution Terminal, 72-fiber, SC/APC, loose tube IFC cable, 2000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Series</b>	IFDT

## General Specifications


<b>Functionality</b>	Patching   Splicing
<b>Adapters, quantity</b>	72
<b>Cable Entry Location</b>	Bottom right   Top right
<b>Cable Type</b>	IFC - Stranded
<b>Color</b>	Putty white
<b>Front Door Type</b>	Double hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface</b>	SC/APC
<b>Interface, stub</b>	No connector
<b>Lock Type</b>	Padlock ready
<b>Mounting</b>	Wall
<b>Port, quantity</b>	72

## Dimensions

<b>Height</b>	599.44 mm   23.6 in
<b>Width</b>	369.82 mm   14.56 in
<b>Depth</b>	127 mm   5 in
<b>Cable Length</b>	609.6 m   2000 ft

# FDT-DJ072NXV2000

## Ordering Tree



## Material Specifications

- Finish** Powder coated
- Material Type** Steel

## Optical Specifications

- Fiber Mode** Singlemode

## Environmental Specifications

- Environmental Space** Indoor
- Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

## Packaging and Weights

- Packaging quantity** 1

# FDT-DJ072NXV2000

---

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant/Exempted

