## 760231514 | HD-2U-SP



High Density 2U Sliding Fiber Splice Panel for holding up to 8 G2 modules (96 duplex LC ports) and Splice Wallet® / RoloSplice® / 360-LP-STACK splice tray kits (between 96 and 192 single fusion splices).

- The panel accommodates up to 8 G2 modules, providing up to 96 duplex LC ports
- The panel accommodates up to 96 single fusion splices when using the Splice Wallet® splice travs
- The panel accommodates up to 128 single fusion splices when using the RoloSplice® splice trays
- The panel accommodates up to 192 single fusion splices when using the 360-LP-STACK fusion splice trays

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch/splice panel

Product Series HD

## General Specifications

Color Black | Gray

Intelligence Type iPatch® ready

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 2

**Shelf Movement** Sliding

#### **Dimensions**

 Height
 88.9 mm | 3.5 in

 Width
 450.85 mm | 17.75 in

**Depth** 501.65 mm | 19.75 in

### Material Specifications

Material Type Steel



# 760231514 | HD-2U-SP

## **Environmental Specifications**

Safety Standard UL 1863

Packaging and Weights

Packaging quantity

**Weight, net** 6.305 kg | 13.9 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



