

CU4022-000 | FOSC-400B4-S24-1-NGNIN29B



FOSC® 400 B4 Fiber Optic Splice Closure, Heat Shrink Cable sealing, one pre-installed 24-splice tray

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability

Asia | EMEA

Product Type

Single-ended, round fiber closure

Product Brand

FOSC®

Product Series

FOSC 400

General Specifications

Cable Entry Drop Port Style

Round

Cable Entry Main Port Style

Oval

Cable Ports Quantity, total

1 oval port (2 cables) + 4 round ports

Cable Sealing Type

Heat shrink

Closure Sealing Type

Dome-to-base clamp with O-ring

Closure Style

Single-ended

Color

Black

Mounting

Pole | Strand | Wall

Network Area Type

Feeder

Splice Tray Included, quantity

1

Splice Tray Type Included

24-way, heat shrink

Splicing Capacity, Mass Fusion, maximum

144

Splicing Capacity, Single Fusion, maximum

96

Splicing Capacity, Single Splice, 12 fibers, maximum

96

Splicing Capacity, Single Splice, 6 fibers, maximum

48

Splicing Type, Supported


Single fusion

Dimensions

CU4022-000 | FOSC-400B4-S24-1-NGNIN29B

Length	540 mm 21.26 in
Diameter	150 mm 5.906 in
Diameter, with clamp	180 mm 7.087 in
Main Cable Diameter, maximum	25 mm 0.984 in

Dimension Drawing



Ordering Tree

CU4022-000 | FOSC-400B4-S24-1-NGNIN29B



^{1H} AB closure can accept a mix of standard and slim trays; please contact your local sales representative.

^{1H} Maximum 8 trays in case of S6 or A6 tray type

^{1H} B closure can initially be fitted with trays; however, retrofitting a standard "B" closure (delivered with 4 trays or fewer) with a 5th and 6th tray is not possible. The B closure can be ordered with up to 5 trays pre-installed and capacity for later addition of a 6th tray (FOSC-400B4XXX/6...).

If 5 or 6 trays are required, a storage basket cannot be used.

^{1H} If 7 or 8 trays are required, a storage basket cannot be used.

Material Specifications

Material Type

Impact-resistant polymer

Environmental Specifications

Environmental Space

Below ground | Buried

Qualification Standards

IEC 61300, 6 m waterhead

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Weight, net

2.5 kg | 5.512 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

**Classification**

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance