

# CV6319-000 | TENIO-B6-NT-0-N



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, no pre-installed trays

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	TENIO™
<b>Product Series</b>	TENIO

## General Specifications

<b>Cable Entry Drop Port Style</b>	Gel block
<b>Cable Entry Main Port Style</b>	Gel block
<b>Cable Ports Quantity, total</b>	6 multi-out ports (30 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Side latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Flash Test Valve</b>	None
<b>Mounting</b>	Wall
<b>Network Area Type</b>	Distribution   Drop
<b>Splice Tray Included, quantity</b>	0
<b>Splice Tray Type Included</b>	No trays
<b>Splices per Tray, quantity</b>	12
<b>Splicing Capacity, Single Fusion, maximum</b>	144
<b>Splicing Type, Supported</b>	Single fusion


## Dimensions

<b>Height</b>	230 mm   9.055 in
---------------	-------------------

# CV6319-000 | TENIO-B6-NT-0-N

<b>Width</b>	134 mm   5.276 in
<b>Length</b>	389 mm   15.315 in
<b>Main Cable Diameter, maximum</b>	16 mm   0.63 in

## Ordering Tree



## Material Specifications

<b>Material Type</b>	Impact-resistant polymer
----------------------	--------------------------

## Environmental Specifications

<b>Environmental Space</b>	Below ground   Buried
<b>Qualification Standards</b>	IEC 61300, 2 m waterhead

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Weight, net</b>	1 kg   2.205 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

