



RABC Copper Closure, butt, unpressurized, heat shrink, 380 mm joint length, for up to 4 cables

- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Unpressurized heat shrink closure
Product Series	RABC

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Color	Black

Dimensions

Length	520 mm 20.472 in
Single Cable Diameter, maximum	70 mm 2.756 in
Single Cable Diameter, minimum	25 mm 0.984 in
Splice Bundle Diameter, maximum	53 mm 2.087 in
Sheath Opening, nominal	380 mm 14.961 in

Material Specifications

Material Type	Polyolefin
----------------------	------------

455586-000 | RABC-100

Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Abrasive strip | Aluminum foil | Branch-off clip | Clamp | O-ring seal | Tie wraps

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

