

XAGA® 1000 Joint closure system for pressurized copper networks, 500 mm sheath opening, 122 mm splice bundle diameter



OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America
Product Type	Pressurized heat shrink closure
Product Brand	XAGA®
Product Series	XAGA 1000


General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	In-line
Color	Black
Mounting	Duct Manhole
Splice Protection Type	Metal canister with valve

Dimensions

Single Cable Diameter, minimum	38 mm 1.496 in
Splice Bundle Diameter, maximum	122 mm 4.803 in
Sheath Opening, nominal	500 mm 19.685 in

Dimension Drawing



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton