


760237029 | NPPR-6-DM-2U-48



Unshielded Recessed Angled Distribution Module Panel, Cat 6, 2U, 48 port, Black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio

NETCONNECT®

Product Type

RJ45 patch panel

General Specifications

ANSI/TIA Category

6

Cable Type

Unshielded

Color

Black

Conductor Type

Solid | Stranded

Modules, quantity

8

Panel Style

Angled recessed

Rack Type

EIA 19 in

Rack Units

2

Termination Type

IDC

Total Ports, quantity

48

Transmission Standards

ANSI/TIA-568.2-D | ISO/IEC 11801 Class E

Wiring

T568A | T568B

Dimensions

Height

88.9 mm | 3.5 in

Width

482.6 mm | 19 in

Depth, with cable management

137.16 mm | 5.4 in

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

Compatible Conductor Gauge, solid

22 AWG | 24 AWG

Compatible Conductor Gauge, stranded

22 AWG | 24 AWG

760237029 | NPPR-6-DM-2U-48

Electrical Specifications

| | |
|--|---|
| Current Rating at Temperature | 1.5 A @ 20 °C 1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1,500 Vac @ 60 Hz |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1,000 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

Material Specifications

| | |
|------------------------------------|---|
| Contact Plating Material | Precious metals |
| Material Type | High-impact, flame retardant, thermoplastic Powder-coated steel |
| Termination Contact Plating | Nickel |

Mechanical Specifications

| | |
|---------------------------------------|----------------------------|
| Plug Insertion Life, minimum | 750 times |
| Plug Insertion Life, test plug | IEC 60603-7 compliant plug |
| Plug Retention Force, minimum | 133 N 29.9 lbf |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | UL cUL |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

760237029 | NPPR-6-DM-2U-48

| | |
|------------|--|
| RCM | Compliant to electrical safety & telecommunications requirements |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

