

Fiber Indexing Terminal, 1x8 Splitter, 4x3 Port Design, 8 Forward Ports, 1 Reverse Port, Dielectric Flat Loose Tube Cable, 100 Feet

- Fiber Indexing terminals are access terminals using hardened connectivity technology that withstand the rugged outside plant environment
- Fiber Indexing terminals eliminate splicing and use 12-strand fiber cable in a daisy-chain topology, reducing the total required cable length by up to 70%
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and play drop cable installations

#### Alternative products available:

HXT-BAHEA0100FN000 NOVUX™ Hardened Indexing Terminal, Full-size Adapter ports, 12F, 1:8 Splitter, 1 Forward port, 1 Reverse port, Dielectric flat loose tube, 100 ft/30 m HMFOC plug (female/no pin) tail

#### **Product Classification**

Regional Availability

North America

**Product Type** Access terminal, indexed with splitter

Product Series NDX

General Specifications

Cable TypeDielectric - Flat - Loose Tube

Cable, quantity 1

**Distribution Type** 1 x 8 splitter

Enclosure Color Black

Forward Port Type Hardened full-size SC/APC adapter

Forward Port, quantity

Mounting Handhole | Pedestal | Pole

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Port, quantity

**Reverse Port Type**Hardened full-size SC/APC

Reverse Port, quantity 1

**Splitter, quantity** 1

Stub Type Hardened multi-fiber (HMFOC) plug

COMMSC PE°

## Dimensions

 Height
 286 mm | 11.26 in


 Width
 187.3 mm | 7.374 in

**Depth** 95 mm | 3.74 in

Cable Length, stub 100 ft (30 m)


**Cable Outer Diameter** 4.5 x 8.1 mm (0.18 x 0.32 in)

## Dimension Drawing



# Ordering Tree





## Material Specifications

Enclosure Material Type	Gasketed hardened plastic
-------------------------	---------------------------

Optical Specifications	
Fiber Type	G.652.D
Operating Wavelength Range	1260 – 1635 nm
Attenuation Cable Coefficient, maximum	0.30 dB/km @ 1550 nm   0.40 dB/km @ 1310 nm
Attenuation Splitter, maximum	10.4 dB
Attenuation Terminal Connectors, maximum	0.45 dB
Directivity, minimum	60 dB
Uniformity, maximum	1 dB
Insertion Loss, Splitter, typical	10 dB
Insertion Loss, Stub Connector, maximum	0.45 dB
Insertion Loss, Stub Connector, typical	0.16 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

Page 3 of 4



Return Loss, Single Ports, minimum

55 dB

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground | Buried

Flammability Rating UL 94 5VA

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead | NEMA, Type 6 + 10 ft

waterhead | Telcordia GR-3120-CORE | Telcordia GR-326-

CORE | Telcordia GR-771-CORE

UV Resistance UV stabilized

Packaging and Weights

Included Enclosure (1) | Optical splitter (1) | Universal mounting bracket (1)

Packaging quantity 1

Packaging Type Box | Carton

Weight, without cable  $1.36 \text{ kg} \mid 2.998 \text{ lb}$ 

## Regulatory Compliance/Certifications

Classification

Compliant

. igo.ic,	
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



**UK-ROHS** 

Agency