CAAHG | IP6A-24PUTP-01S-PG2S

Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to dual row standard density RJ45 plug, 24 links

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED X10D® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6A

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector A Information outlet

Interface Feature, connector A Single row | Standard density

Interface, Connector B RJ45 plug

Interface Feature, connector B Dual row | Standard density

Link Count 24

Wiring T568B

Dimensions

Cable Assembly Length Range (m) 2 - 30

Cable Assembly Length Range (ft) 7 - 98

Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



CAAHG | IP6A-24PUTP-01S-PG2S



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Plenum
Flammability Rating UL 94 V-0

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

123 – GigaSPEED X10D® 2095B Category 6A U/UTP Cable, plenum, 4 pair

count

MGS600 - GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded



GigaSPEED X10D® 2095B Category 6A U/UTP Cable, plenum, 4 pair count

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Twisted pair cable
Product Brand GigaSPEED X10D®

General Specifications

Product Number 2095B
ANSI/TIA Category 6A

Cable Component Type Cordage

Cable Type U/UTP (unshielded)

Conductor Type, singlesSolidConductors, quantity8Pairs, quantity4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D


Dimensions

Diameter Over Jacket, nominal7.239 mm | 0.285 inJacket Thickness1.524 mm | 0.06 in

Conductor Gauge, singles 24 AWG

Cross Section Drawing





Electrical Specifications

Characteristic Impedance 100 ohm

Characteristic Impedance Tolerance $\pm 15 \text{ ohm}$ dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 9.38 ohms/100 m | 2.859 ohms/100 ft

Dielectric Strength, minimum1500 Vac | 2500 VdcMutual Capacitance at Frequency6.0 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 67 %

Operating Frequency, maximum 550 MHz

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating 300 V

Material Specifications

Conductor Material Bare copper

Insulation MaterialFEPJacket MaterialPVCSeparator MaterialFEP

Page 4 of 7

123

Separator 2 Material Polyolefin

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental SpacePlenumFlame Test MethodCMP/FT6Smoke Test MethodCMP/FT6

Packaging and Weights

Cable weight 61.878 kg/km | 41.58 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

MGS600

Base Product



GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type Modular jack

Product Brand GigaSPEED X10D®

Product Series MGS600

General Specifications

ANSI/TIA Category 6A

Cable Type Unshielded

Conductor Type Solid | Stranded

Termination Type IDC

Wiring T568A | T568B

Dimensions

 Height
 19.4 mm | 0.764 in

 Width
 21.08 mm | 0.83 in

 Depth
 30.2 mm | 1.189 in

 Compatible Conductor Gauge, solid
 22 AWG | 24 AWG

Compatible Conductor Gauge, stranded 22 AWG | 24 AWG

Electrical Specifications

 Contact Resistance Variation, maximum
 20 mOhm

 Contact Resistance, maximum
 100 mOhm

Page 6 of 7

MGS600

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

PoE Durability Supports IEEE 802.3bt Type 4 (90 W) applications after 3000

plug to jack mating cycles

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | High-impact, flame retardant, thermoplastic

Termination Contact Plating Nickel

Mechanical Specifications

Plug Retention Force, minimum 133 N | 29.9 lbf

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative HumidityUp to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

