

CHTXC | IPO6-08RUTP-1LK08-BLUNT

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Riser Preterminated Copper Cable, dual row OneLink 2x4 to unterminated, 8 links

This product will be discontinued on: January 31, 2025

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Copper trunk cable assembly
Product Brand	GigaSPEED XL® InstaPATCH® Cu

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	OneLink 2x4
Interface Feature, connector A	Standard
Interface, Connector B	Unterminated
Link Count	8
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	2 – 30
Cable Assembly Length Range (ft)	7 – 98

Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

Ordering Tree

CHTXC | IPO6-08RUTP-1LK08-BLUNT

1 2 3 4 5 6 7 8 9 10 11 12											
C A A A C - 1 1 H A B B F O S O											
Cable Type											
A	Cat 6A X10D – U/UTP (Plenum)										
B	Cat 6A X10D – U/UTP (Riser)										
C	Cat 6A X10D – U/UTP (LSZH)										
D	Cat 6A X10D – F/UTP (Plenum)										
E	Cat 6A X10D – F/UTP (Riser)										
F	Cat 6A X10D – F/UTP (LSZH)										
G	Cat 6 XL – U/UTP (Plenum)										
H	Cat 6 XL – U/UTP (Riser)										
J	Cat 6 XL – U/UTP (LSZH)										
Q	Cat 6A X10D – S/FTP (LSZH)										
R	Cat 6 – U/UTP Class B Rated (LSZH)										
S	Cat 6A – U/UTP Class B Rated (LSZH)										
Y	Cat 6A X10D SD – U/UTP (Riser)										
Connector B											
A	Outlet* – Single Row Standard Density										
B	Outlet* – Dual Row Standard Density										
C	Outlet* – Dual Row High Density										
G	RJ45 Plug* – Single Row Standard Density										
H	RJ45 Plug* – Dual Row Standard Density										
J	RJ45 Plug* – Dual Row High Density										
N	1100 Module										
R	360 1100 Evolve Module										
S	OneLink 2x6										
T	OneLink 2x4										
Orientation A											
1	Trident Series Flat										
2	Right Paired Flat										
3	Right Series Flat										
4	Left Paired Flat										
5	Left Series Flat										
6	Trident Paired Flat										
A	Trident Series Angled										
B	Right Paired Angled										
C	Right Series Angled										
D	Left Paired Angled										
E	Left Series Angled										
F	Trident Paired Angled										
Orientation B											
1	Trident Series Flat										
2	Right Paired Flat										
3	Right Series Flat										
4	Left Paired Flat										
5	Left Series Flat										
6	Trident Paired Flat										
A	Trident Series Angled										
B	Right Paired Angled										
C	Right Series Angled										
D	Left Paired Angled										
E	Left Series Angled										
F	Trident Paired Angled										
X	Not Applicable										
Connector A											
A	Outlet* – Single Row Standard Density										
B	Outlet* – Dual Row Standard Density										
C	Outlet* – Dual Row High Density										
G	RJ45 Plug* – Single Row Standard Density										
H	RJ45 Plug* – Dual Row Standard Density										
J	RJ45 Plug* – Dual Row High Density										
N	1100 Module										
R	360 1100 Evolve Module										
S	OneLink 2x6										
T	OneLink 2x4										
X	Unterminated										
Link											
B	6										
C	8										
D	12										
E	16										
F	18										
G	24										
Bundling											
H	Hook-n-loop										
S	Sleeving										
Labeling											
A	Generic Label										
Outlet Color											
0	Not Applicable										
1	Black (BK)										
2	Blue (BL)										
8	White (WH)										
Jacket Color											
8	White (WH)										
C	Slate (SL)										
Z	Blue (BL)										
UOM											
F	Foot										
M	Meter										
Length											
12	XXX										

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Riser
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

1071E-4/23	–	GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, 4 pair count
------------	---	---

1071E-4/23



GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, 4 pair count

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair cable
Product Brand	GigaSPEED XL®
Ordering Note	Not available in Europe, the Middle East, or Africa


General Specifications

Product Number	1071E
ANSI/TIA Category	6
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Pairs, quantity	4
Separator Type	Bisector
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Dimensions

Diameter Over Jacket, nominal	5.893 mm 0.232 in
Jacket Thickness	0.559 mm 0.022 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	7.61 ohms/100 m 2.32 ohms/100 ft
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	300 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC
Separator Material	Polyolefin

Mechanical Specifications

1071E-4/23

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Non-plenum

Temperature Rating, UL 75 °C | 167 °F

Flame Test Method CMG | CMR

Packaging and Weights

Cable weight 38.097 kg/km | 25.6 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system