


# A3XMXMPAL

## Base Product



OM4 MPO-12 (Pinned) to MPO-12 (Unpinned), Pre-terminated Trunk Cable, 96-Fiber, LSZH B2ca, Method A

### OBSOLETE

This product was discontinued on: April 30, 2024

#### Replaced By:

A3XMXMPCL

OM4 MPO-12 (Pinned) to MPO-12 (Unpinned), Pre-terminated Trunk Cable, 96-Fiber, LSZH B2ca, Method A

## Product Classification

|                              |                                                                                                                          |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| <b>Regional Availability</b> | Europe                                                                                                                   |
| <b>Portfolio</b>             | CommScope®                                                                                                               |
| <b>Product Type</b>          | Fiber trunk cable assembly                                                                                               |
| <b>Ordering Note</b>         | For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |


## General Specifications

|                               |                   |
|-------------------------------|-------------------|
| <b>Color, boot A</b>          | Black             |
| <b>Color, connector A</b>     | Aqua              |
| <b>Color, boot B</b>          | Black             |
| <b>Color, connector B</b>     | Aqua              |
| <b>Construction Type</b>      | Stranded          |
| <b>Furcation Color</b>        | Aqua              |
| <b>Interface, Connector A</b> | MPO-12/UPC Male   |
| <b>Interface, Connector B</b> | MPO-12/UPC Female |
| <b>Jacket Color</b>           | Aqua              |
| <b>Polarity</b>               | Method A          |

# A3XMXMPAL

|                                         |          |
|-----------------------------------------|----------|
| <b>Fibers per Subunit, quantity</b>     | 12       |
| <b>Total Fibers, quantity</b>           | 96       |
| <b>Dimensions</b>                       |          |
| <b>Cable Assembly Length Range (m)</b>  | 3 – 999  |
| <b>Cable Assembly Length Range (ft)</b> | 10 – 999 |

## Ordering Tree



## Mechanical Specifications

|                                          |                               |
|------------------------------------------|-------------------------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0°   4.40 lb @ 90° |
|------------------------------------------|-------------------------------|

## Optical Specifications

|                   |                 |
|-------------------|-----------------|
| <b>Fiber Mode</b> | Multimode       |
| <b>Fiber Type</b> | OM4, LazrSPEED® |

## Environmental Specifications

|                                                     |                                        |
|-----------------------------------------------------|----------------------------------------|
| <b>Operating Temperature</b>                        | -10 °C to +60 °C (+14 °F to +140 °F)   |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca                                   |
| <b>Environmental Space</b>                          | Indoor   Low Smoke Zero Halogen (LSZH) |

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                                                                 |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| ANATEL        | Compliant                                                                                                                      |
| CHINA-ROHS    | Above maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |

# A3XMXMPAL

---

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



## Included Products

- 760239603 N-096-MP-5K-F12AQ/B2 – Fiber indoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber, 12 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca Flame rating
- 860366210 – MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm
- 860366228 – MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

# 760239603 | N-096-MP-5K-F12AQ/B2

---



Fiber indoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber, 12 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca Flame rating

## Product Classification

|                              |                    |
|------------------------------|--------------------|
| <b>Regional Availability</b> | Asia   EMEA        |
| <b>Portfolio</b>             | CommScope®         |
| <b>Product Type</b>          | Fiber indoor cable |
| <b>Product Series</b>        | N-MP               |

## General Specifications

|                          |                 |
|--------------------------|-----------------|
| <b>Cable Type</b>        | MPO trunk cable |
| <b>Construction Type</b> | Non-armored     |
| <b>Subunit Type</b>      | Gel-free        |
| <b>Jacket Color</b>      | Aqua            |
| <b>Jacket Marking</b>    | Feet            |
| <b>Subunit, quantity</b> | 8               |
| <b>Total Fiber Count</b> | 96              |

## Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 3 mm   0.118 in    |
| <b>Diameter Over Jacket</b>         | 13.6 mm   0.535 in |

## Representative Image



## Mechanical Specifications

|                                          |                                       |
|------------------------------------------|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 206 mm   8.11 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 137 mm   5.394 in                     |
| <b>Tensile Load, long term, maximum</b>  | 400 N   89.924 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 1335 N   300.12 lbf                   |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 25 cycles                             |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 2.94 N-m   26.021 in lb               |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 226 m   741.47 ft                     |

## Optical Specifications

|                   |                                           |
|-------------------|-------------------------------------------|
| <b>Fiber Type</b> | OM4, LazrSPEED® 550   OM4, LazrSPEED® 550 |
|-------------------|-------------------------------------------|

## Environmental Specifications

|                                 |                                      |
|---------------------------------|--------------------------------------|
| <b>Installation temperature</b> | 0 °C to +50 °C (+32 °F to +122 °F)   |
| <b>Operating Temperature</b>    | 0 °C to +60 °C (+32 °F to +140 °F)   |
| <b>Storage Temperature</b>      | -40 °C to +70 °C (-40 °F to +158 °F) |

# 760239603 | N-096-MP-5K-F12AQ/B2

|                                                     |                                       |
|-----------------------------------------------------|---------------------------------------|
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca                                  |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a                                   |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d0                                    |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1                                    |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)         |
| <b>Flame Test Method</b>                            | IEC 60754-2   IEC 61034-2             |

## Environmental Test Specifications

|                                      |                                    |
|--------------------------------------|------------------------------------|
| <b>Heat Age</b>                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                     |
| <b>Low High Bend</b>                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11          |
| <b>Temperature Cycle</b>             | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|                     |                            |
|---------------------|----------------------------|
| <b>Cable weight</b> | 181 kg/km   121.626 lb/kft |
|---------------------|----------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                          |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available                                                                 |
| CHINA-ROHS    | Below maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant                                                                                                                      |
| UK-ROHS       | Compliant                                                                                                                      |



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# 860366210

---



MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

## Product Classification

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®                                                          |
| <b>Product Type</b>          | Fiber connector                                                     |
| <b>Product Brand</b>         | LazrSPEED®                                                          |

## General Specifications

|                          |                |
|--------------------------|----------------|
| <b>Color</b>             | Aqua           |
| <b>Color, boot</b>       | Black          |
| <b>Ferrule Geometry</b>  | Flat           |
| <b>Interface</b>         | MPO/UPC Female |
| <b>Interface Feature</b> | Unpinned       |
| <b>Total Fiber Count</b> | 12             |

## Dimensions

|                                  |                    |
|----------------------------------|--------------------|
| <b>Length</b>                    | 60.1 mm   2.366 in |
| <b>Compatible Cable Diameter</b> | 3 mm   0.118 in    |

## Material Specifications

|                         |         |
|-------------------------|---------|
| <b>Ferrule Material</b> | Polymer |
|-------------------------|---------|

## Mechanical Specifications

|                                          |                |
|------------------------------------------|----------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0 ° |
|------------------------------------------|----------------|

## Optical Specifications

|                                      |           |
|--------------------------------------|-----------|
| <b>Fiber Mode</b>                    | Multimode |
| <b>Fiber Type</b>                    | OM3   OM4 |
| <b>Insertion Loss Change, mating</b> | 0.3 dB    |

# 860366210

---

|                                           |                  |
|-------------------------------------------|------------------|
| <b>Optical Components Standard</b>        | ANSI/TIA-568-C.3 |
| <b>Insertion Loss Change, temperature</b> | 0.3 dB           |
| <b>Insertion Loss, maximum</b>            | 0.2 dB           |
| <b>Return Loss, minimum</b>               | 27 dB            |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                          |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS    | Below maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant                                                                                                                      |
| UK-ROHS       | Compliant/Exempted                                                                                                             |




## \* Footnotes

|                                           |                                                                         |
|-------------------------------------------|-------------------------------------------------------------------------|
| <b>Insertion Loss Change, mating</b>      | TIA-568: Maximum insertion loss change after 500 matings                |
| <b>Insertion Loss Change, temperature</b> | Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F) |



# 860366228

---



MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

## Product Classification

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®                                                          |
| <b>Product Type</b>          | Fiber connector                                                     |
| <b>Product Brand</b>         | LazrSPEED®                                                          |

## General Specifications

|                          |              |
|--------------------------|--------------|
| <b>Color</b>             | Aqua         |
| <b>Color, boot</b>       | Black        |
| <b>Ferrule Geometry</b>  | Flat         |
| <b>Interface</b>         | MPO/UPC Male |
| <b>Interface Feature</b> | Pinned       |
| <b>Total Fiber Count</b> | 12           |

## Dimensions

|                                  |                    |
|----------------------------------|--------------------|
| <b>Length</b>                    | 60.1 mm   2.366 in |
| <b>Compatible Cable Diameter</b> | 3 mm   0.118 in    |

## Material Specifications

|                         |         |
|-------------------------|---------|
| <b>Ferrule Material</b> | Polymer |
|-------------------------|---------|

## Mechanical Specifications

|                                          |                |
|------------------------------------------|----------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0 ° |
|------------------------------------------|----------------|

## Optical Specifications

|                                      |                  |
|--------------------------------------|------------------|
| <b>Fiber Mode</b>                    | Multimode        |
| <b>Fiber Type</b>                    | OM3   OM4        |
| <b>Insertion Loss Change, mating</b> | 0.3 dB           |
| <b>Optical Components Standard</b>   | ANSI/TIA-568-C.3 |

# 860366228

---

|                                           |        |
|-------------------------------------------|--------|
| <b>Insertion Loss Change, temperature</b> | 0.3 dB |
| <b>Insertion Loss, maximum</b>            | 0.2 dB |
| <b>Return Loss, minimum</b>               | 27 dB  |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                          |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS    | Above maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted                                                                                                             |
| UK-ROHS       | Compliant/Exempted                                                                                                             |



### \* Footnotes

|                                           |                                                                         |
|-------------------------------------------|-------------------------------------------------------------------------|
| <b>Insertion Loss Change, mating</b>      | TIA-568: Maximum insertion loss change after 500 matings                |
| <b>Insertion Loss Change, temperature</b> | Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F) |