

F1A-TNRNR-M815-C4



FSJ1-50A SureFlex® Jumper with interface types N Male Right Angle and N Male Right Angle, 0.815 m

OBSOLETE

This product was discontinued on: January 29, 2008

Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	N Male
Orientation	0°
Specification Sheet Revision Level	A

Dimensions

Length	0.815 m 2.674 ft
Nominal Size	1/4 in

Electrical Specifications


3rd Order IMD	-80 dBm
DTF, Connector A	-29.5 dB
DTF, Connector B	-29.5 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
400–2200 MHz	1.2	20.83

Jumper Assembly Sample Label

F1A-TNRNR-M815-C4



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- | | | |
|------------|---|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 35422-33 | - | Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket |
| 35422-75 | - | Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket |
| FSJ1-50A | - | FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket |
| FSJ1RK-50A | - | FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a d0 a1 Compliant |