

F2A-PDRDF-96N



FSJ2-50 SureFlex® Jumper with interface types 7-16 DIN Male Right Angle and 7-16 DIN Female Bulkhead, 2.44 m

OBSOLETE

This product was discontinued on: December 1, 2016

Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Bulkhead
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Orientation	0°
Specification Sheet Revision Level	A

Dimensions

Length	2.44 m 8.005 ft
Nominal Size	3/8 in

Electrical Specifications

DTF, Connector A	-32 dB
DTF, Connector B	-32 dB

Jumper Assembly Sample Label

F2A-PDRDF-96N



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance



Included Products

35422-42	- Heat Treated FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
FSJ2-50	- FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket