

ATCB-B01-010



AISG RET Control Cable, 10 m

- Feeds data and power to RET system components
- AISG and RoHS compliant

Product Classification

Product Type AISG standard cable

General Specifications

AISG Connector A 8-pin DIN Female

AISG Connector A Body Style Straight

AISG Connector A Standard IEC 60130-9

AISG Connector B 8-pin DIN Male

AISG Connector B Body Style Straight

AISG Connector B Standard IEC 60130-9

Color Black

Data Conductor Type 0.24 mm² (24 AWG) twisted pair

EU Certification CB | CE

Power Conductor Type 0.82 mm² (18 AWG) stranded

Total Conductors, quantity 6

Dimensions

Length 10 m | 32.808 ft

Diameter Over Jacket 8 mm | 0.315 in

Electrical Specifications

Protocol AISG 1.1 | AISG 2.0

Voltage, maximum 300 V

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 100%

ATCB-B01-010

Climatic Sequence Test Method	IEC 60068-2-14
Cold Exposure Test Method	IEC 60068-2-1
Damp Heat Exposure Test Method	IEC 60068-2-30, Test Condition Db
Heat Exposure Test Method	IEC 60068-2-2
Ingress Protection Test Method	IEC 60529:2001, IP67
Rain Simulation Test Method	IEC 60068-2-18, Test Condition Ra, Method 1
UV Resistance Test Method	IEC 60068-2-5, Test Condition B

Packaging and Weights

Weight, net 0.9 kg | 1.984 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

