CMAX-0-43-UW-153



Cell-Max[™] Low PIM Omni In-building Antenna, 617–6000 MHz (Recessed ceiling mount kit PN:7760591 sold separately)

Product Classification

Product Type In-building antenna

Product Brand Cell-Max[™]

General Specifications

ApplicationIndoorAntenna TypeOmniAntenna Array CharacteristicSISOPolarizationVertical

Color White (RAL 9016)

Mounting Thru-hole ceiling mount (optional)

Number of Ports

Pigtail Cable670-141SXE, plenum ratedRadome MaterialASA+PC, UV stabilized

RF Connector Interface 4.3-10 Female

Dimensions

 Height
 82 mm | 3.228 in

 Pigtail Length
 500 mm | 19.685 in

 Outer Diameter
 206 mm | 8.11 in

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1400 – 1600 MHz | 1710 – 2700 MHz | 3300 – 4200 MHz | 5150 – 5925 MHz | 617 –

698 MHz | 698 - 960 MHz

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

COMMSC PE°

CMAX-0-43-UW-I53

Frequency Band, MHz	617-698	698-960	1400-1600	1710-2700	3300-4200	5150-5925
Gain, dBi	2.1	2.1	3	4	4.3	5.4
Beamwidth, Horizontal, degrees	360	360	360	360	360	360
VSWR Return loss, dB	1.7 11.7	1.5 14.0	1.7 11.7	1.5 14.0	1.6 12.7	1.6 12.7
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	
Input Power per Port, maximum, watts	100	100	100	100	100	100

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (-40 \,^{\circ}F to } +140 \,^{\circ}\text{F)}$

Relative Humidity Up to 100%

Packaging and Weights

 Height, packed
 210 mm | 8.268 in

 Width, packed
 190 mm | 7.48 in

 Length, packed
 210 mm | 8.268 in

Packaging quantity

 Weight, gross
 0.6 kg | 1.323 lb

 Weight, net
 0.4 kg | 0.882 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant





