

4-port small cell antenna, 4x 3300-5000 MHz. 360° Horizontal Beamwidth, fixed tilt.

- Light weight, low profile omnidirectional antenna ideal for low to moderate gain applications
- Compact and small footprint, space-saving design for high-density environments
- Supports up to 4T4R applications

General Specifications

Antenna Type Small Cell
Band Single band

Color Light Gray (RAL 7035)

Grounding Type RF connector inner conductor and body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radome Material ASA, UV stabilized

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 4

RF Connector Quantity, total 4

Dimensions

 Width
 200 mm | 7.874 in

 Depth
 200 mm | 7.874 in

 Length
 600 mm | 23.622 in

 Net Weight, without mounting kit
 4.7 kg | 10.362 lb

Port Configuration





Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 3300 – 5000 MHz

 ${\bf Polarization} \hspace{2cm} \pm 45^{\circ}$ ${\bf Total Input Power, maximum} \hspace{2cm} 360 \ W$

Electrical Specifications

Frequency Band, MHz	3300-3600	3550-3700	3600-3900	3900-4200	4200-4500	4500-5000
Gain, dBi	11.5	11.7	11.6	11.9	11.7	14.1
Beamwidth, Horizontal, degrees	360	360	360	360	360	360
Beamwidth, Vertical, degrees	9.1	9.1	8.5	7.8	7.1	6.7
Beam Tilt, degrees	4	4	4	4	4	4
USLS (First Lobe), dB	15	15	15	15	15	15
Isolation, Cross Polarization, dB	25	25	25	25	25	25

Page 2 of 4

Isolation, Inter-band, dB	28	28	28	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
Input Power per Port at 50°C, maximum, watts	125	125	125	125	125	125

Electrical Specifications, BASTA

Frequency Band, MHz	3300-3600	3550-3700	3600-3900	3900-4200	4200-4500	4500-5000
Gain by all Beam Tilts, average, dBi	11.2	11.2	11.3	11.4	11.4	13.3
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.4	±0.4	±0.7	±0.4	±1.8
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.8	±1	±0.9	±1	±0.8

Mechanical Specifications

Wind Loading @ Velocity, frontal	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	150.0 N @ 150 km/h (33.7 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

Width, packed	300 mm	11.811 in
Depth, packed	320 mm	12.598 in
Length, packed	850 mm	33.465 in
Weight, gross	7.3 kg 16	5.094 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted





* Footnotes



Performance Note

Severe environmental conditions may degrade optimum performance