

VHLP2-X8023-DET



0.6 m | 2 ft ValuLine® High Performance Low Profile Antenna, dual band, dual polarised 71.000 – 86.000 GHz and single polarised 21.200 – 23.600 GHz, OEM custom flange

Product Classification

| | |
|----------------------|-------------------|
| Product Type | Microwave antenna |
| Product Brand | ValuLine® |

General Specifications

| | |
|-------------------------------|--|
| Antenna Type | VHLP - ValuLine® High Performance Low Profile Antenna, dual band |
| Polarization | Dual 80 GHz, Single 23 GHz |
| Antenna Input | OEM specific |
| Antenna Color | White |
| Reflector Construction | One-piece reflector |
| Radome Color | Gray |
| Radome Material | Composite Broadband |
| Flash Included | No |
| Side Struts, Included | 0 |
| Side Struts, Optional | 0 |

Dimensions

| | |
|--------------------------|--------------|
| Diameter, nominal | 0.6 m 2 ft |
|--------------------------|--------------|

Electrical Specifications

| | |
|---|---------------------|
| Operating Frequency Band | 71.000 – 86.000 GHz |
| Gain, Low Band | 48.5 dBi |
| Gain, Mid Band | 49.5 dBi |
| Gain, Top Band | 50 dBi |
| Boresite Cross Polarization Discrimination (XPD) | 27 dB |
| Front-to-Back Ratio | 68 dB |
| Beamwidth, Horizontal | 0.5 ° |

VHLP2-X8023-DET

| | |
|---|--|
| Beamwidth, Vertical | 0.5 ° |
| Return Loss | 15 dB |
| VSWR | 1.43 |
| Radiation Pattern Envelope Reference (RPE) | 7442 |
| Electrical Compliance | ETSI 302 217 Class 3 US FCC Part 101.115 |

Electrical Specifications, Band 2


| | |
|--|--|
| Operating Frequency Band | 21.200 – 23.600 GHz |
| Gain, Low Band | 39.3 dBi |
| Gain, Mid Band | 39.4 dBi |
| Gain, Top Band | 39.5 dBi |
| Beamwidth, Horizontal | 1.5 ° |
| Beamwidth, Vertical | 1.5 ° |
| Boresite Cross Polarization Discrimination (XPD) | 30 dB |
| Boresite Cross Polarization Discrimination (XPD) Note | 30 dB typical and subject to change without notice |
| Electrical Compliance | Canada SRSP 321.8 B ETSI 302 217 Class 3 FCC Cat A |
| Front-to-Back Ratio | 66 dB |
| Radiation Pattern Envelope Reference (RPE) | 7441 |
| Return Loss | 15 dB |
| VSWR | 1.43 |

Mechanical Specifications

| | |
|--|------------------------------|
| Compatible Mounting Pipe Diameter | 50 mm–115 mm 2.0 in–4.5 in |
| Fine Azimuth Adjustment Range | ±9° |
| Fine Elevation Adjustment Range | ±15° |
| Wind Speed at 23 GHz, operational | 180 km/h 111.847 mph |
| Wind Speed at 80 GHz, operational | 144 km/h 89.477 mph |
| Wind Speed, survival | 250 km/h 155.343 mph |

Antenna Dimensions and Mounting Information

VHLP2-X8023-DET



| Dimensions in mm (Inches) | | | | | | |
|---------------------------|------------|------------|------------|-----------|------------|------------|
| Antenna Size, ft (m) | A | B | C | D | E | F |
| 2 (0.6) | 660 (25.9) | 309 (12.2) | 279 (10.9) | 106 (4.2) | 459 (18.1) | 505 (19.8) |

Wind Forces at Wind Velocity Survival Rating

| | |
|-----------------------------|---------------------------|
| Axial Force (FA) | 1693 N 380.602 lbf |
| Side Force (FS) | 814 N 182.995 lbf |
| Twisting Moment (MT) | 756 N-m 6,691.164 in lb |
| Zcg without Ice | 9 mm 0.354 in |

Packaging and Weights

| | |
|-----------------------|---|
| Height, packed | 600 mm 23.622 in |
| Width, packed | 740 mm 29.134 in |
| Length, packed | 740 mm 29.134 in |
| Packaging Type | Standard pack |
| Volume | 0.3 m ³ 10.594 ft ³ |
| Weight, gross | 23 kg 50.706 lb |
| Weight, net | 17 kg 37.479 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

VHLP2-X8023-DET

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Frequency Band

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Gain, Mid Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Boresite Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Return Loss

The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.

VSWR

Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.

Radiation Pattern Envelope Reference (RPE)

Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular accuracy of $\pm 1^\circ$ throughout

Radiation Pattern Envelope Reference (RPE)

Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular accuracy of $\pm 1^\circ$ throughout

Wind Speed, survival

The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Side Force (FS)

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

VHLP2-X8023-DET

Twisting Moment (MT)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Packaging Type

Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.