

F2A-HMHR-1M5-TMB

FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male Right angle, 1.5 M



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|-----------------------|--------------------------------------|
| Product Type | Wireless transmission cable assembly |
| Product Series | FSJ2-50 |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 1.5 m 4.921 ft |
| Nominal Size | 3/8 in |

Electrical Specifications

| | |
|----------------------------------|----------------------|
| 3rd Order IMD | -117 dBm |
| 3rd Order IMD Test Method | Two +43 dBm carriers |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz | 1.1 | 26.45 |
| 1700–2200 MHz | 1.1 | 26.45 |
| 2200–2700 MHz | 1.1 | 26.45 |

Jumper Assembly Sample Label

F2A-HMHR-1M5-TMB



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Included Products

FSJ2-50 – FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket