

F4S-HPHMHM-8M-SGW



RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 with HELIAX® SureGuard weatherproofing, 8 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 8 m 26.247 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -119 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) | VSWR, typical | Return Loss, typical (dB) |
|----------------|-------|------------------|---------------|---------------------------|
| 698–960 MHz | 1.106 | 25.96 | | |
| 1700–2200 MHz | 1.106 | 25.96 | | |

F4S-HPHMHM-8M-SGW

2200–2700 MHz

1.135 23.98

3400–3800 MHz

1.222

20.01

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

RSJ4-50 – RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

RSJ4-50



RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

Product Classification

| | |
|-----------------------|--------------------------------------|
| Product Type | Coaxial wireless cable |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |
| Ordering Note | CommScope® standard product (Global) |

General Specifications

| | |
|-------------------------|--|
| Flexibility | Superflexible |
| Jacket Color | Black |
| Performance Note | Attenuation values typical, guaranteed within 5% |

Dimensions

| | |
|---------------------------------|----------------------|
| Diameter Over Dielectric | 9.423 mm 0.371 in |
| Diameter Over Jacket | 13.411 mm 0.528 in |
| Inner Conductor OD | 3.594 mm 0.141 in |
| Outer Conductor OD | 11.989 mm 0.472 in |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---------------------------------------|------------------------------------|
| Cable Impedance | 50 ohm \pm 1 ohm |
| Capacitance | 83.9 pF/m 25.573 pF/ft |
| dc Resistance, Inner Conductor | 2.65 ohms/km 0.808 ohms/kft |
| dc Resistance, Outer Conductor | 4.56 ohms/km 1.39 ohms/kft |
| dc Test Voltage | 2500 V |
| Inductance | 0.213 μ H/m 0.065 μ H/ft |

RSJ4-50

| | |
|--|-----------------|
| Insulation Resistance | 100000 MOhms-km |
| Jacket Spark Test Voltage (rms) | 5000 V |
| Operating Frequency Band | 1 – 10200 MHz |
| Peak Power | 15.6 kW |
| Velocity | 79 % |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|-----------------------|-------------|-------------------------|
| 680–800 MHz | 1.201 | 20.79 |
| 800–960 MHz | 1.201 | 20.79 |
| 1700–2200 MHz | 1.201 | 20.79 |
| 2300–2700 MHz | 1.201 | 20.79 |

Attenuation

| Frequency (MHz) | Attenuation (dB/100 m) | Attenuation (dB/100 ft) | Average Power (kW) |
|------------------------|-------------------------------|--------------------------------|---------------------------|
| 1.0 | 0.327 | 0.1 | 15.6 |
| 1.5 | 0.401 | 0.122 | 15.6 |
| 2.0 | 0.463 | 0.141 | 15.6 |
| 10.0 | 1.044 | 0.318 | 10.14 |
| 20.0 | 1.485 | 0.453 | 7.12 |
| 30.0 | 1.828 | 0.557 | 5.79 |
| 50.0 | 2.377 | 0.724 | 4.45 |
| 85.0 | 3.13 | 0.954 | 3.38 |
| 88.0 | 3.187 | 0.971 | 3.32 |
| 100.0 | 3.406 | 1.038 | 3.11 |
| 108.0 | 3.546 | 1.081 | 2.98 |
| 150.0 | 4.214 | 1.285 | 2.51 |
| 174.0 | 4.558 | 1.389 | 2.32 |
| 200.0 | 4.908 | 1.496 | 2.16 |
| 204.0 | 4.96 | 1.512 | 2.13 |
| 300.0 | 6.095 | 1.858 | 1.74 |
| 400.0 | 7.121 | 2.17 | 1.49 |
| 450.0 | 7.592 | 2.314 | 1.39 |
| 460.0 | 7.684 | 2.342 | 1.38 |
| 500.0 | 8.042 | 2.451 | 1.32 |

RSJ4-50

| | | | |
|---------------|--------|-------|------|
| 512.0 | 8.148 | 2.483 | 1.3 |
| 600.0 | 8.891 | 2.71 | 1.19 |
| 700.0 | 9.683 | 2.951 | 1.09 |
| 800.0 | 10.431 | 3.179 | 1.01 |
| 824.0 | 10.605 | 3.232 | 1 |
| 894.0 | 11.101 | 3.383 | 0.95 |
| 960.0 | 11.555 | 3.522 | 0.92 |
| 1000.0 | 11.824 | 3.604 | 0.89 |
| 1218.0 | 13.226 | 4.031 | 0.8 |
| 1250.0 | 13.423 | 4.091 | 0.79 |
| 1500.0 | 14.906 | 4.543 | 0.71 |
| 1700.0 | 16.027 | 4.885 | 0.66 |
| 1794.0 | 16.537 | 5.04 | 0.64 |
| 1800.0 | 16.57 | 5.05 | 0.64 |
| 2000.0 | 17.624 | 5.371 | 0.6 |
| 2100.0 | 18.137 | 5.528 | 0.58 |
| 2200.0 | 18.641 | 5.682 | 0.57 |
| 2300.0 | 19.138 | 5.833 | 0.55 |
| 2500.0 | 20.11 | 6.129 | 0.53 |
| 2700.0 | 21.056 | 6.418 | 0.5 |
| 3000.0 | 22.432 | 6.837 | 0.47 |
| 3400.0 | 24.198 | 7.375 | 0.44 |
| 3600.0 | 25.055 | 7.636 | 0.42 |
| 3700.0 | 25.478 | 7.765 | 0.42 |
| 3800.0 | 25.898 | 7.893 | 0.41 |
| 3900.0 | 26.314 | 8.02 | 0.4 |
| 4000.0 | 26.727 | 8.146 | 0.4 |
| 4100.0 | 27.136 | 8.271 | 0.39 |
| 4200.0 | 27.542 | 8.394 | 0.38 |
| 4300.0 | 27.946 | 8.517 | 0.38 |
| 4400.0 | 28.346 | 8.639 | 0.37 |
| 4500.0 | 28.744 | 8.761 | 0.37 |
| 4600.0 | 29.139 | 8.881 | 0.36 |
| 4700.0 | 29.531 | 9.001 | 0.36 |
| 4800.0 | 29.921 | 9.119 | 0.35 |

RSJ4-50

| | | | |
|----------------|--------|--------|------|
| 4900.0 | 30.308 | 9.238 | 0.35 |
| 5000.0 | 30.693 | 9.355 | 0.34 |
| 6000.0 | 34.427 | 10.493 | 0.31 |
| 8000.0 | 41.403 | 12.619 | 0.26 |
| 8800.0 | 44.054 | 13.427 | 0.24 |
| 10000.0 | 47.914 | 14.603 | 0.22 |

Material Specifications

| | |
|---------------------------------|---------------------------|
| Dielectric Material | Foam PE |
| Jacket Material | PE |
| Inner Conductor Material | Copper-clad aluminum wire |
| Outer Conductor Material | Corrugated copper |

Mechanical Specifications

| | |
|--|-------------------------|
| Minimum Bend Radius, multiple Bends | 31.75 mm 1.25 in |
| Minimum Bend Radius, single Bend | 31.75 mm 1.25 in |
| Number of Bends, minimum | 15 |
| Number of Bends, typical | 20 |
| Tensile Strength | 79 kg 174.165 lb |
| Bending Moment | 3.1 N-m 27.437 in lb |
| Flat Plate Crush Strength | 2 kg/mm 111.995 lb/in |

Environmental Specifications

| | |
|---|--------------------------------------|
| Installation temperature | -40 °C to +60 °C (-40 °F to +140 °F) |
| Operating Temperature | -55 °C to +85 °C (-67 °F to +185 °F) |
| Storage Temperature | -70 °C to +85 °C (-94 °F to +185 °F) |
| Attenuation, Ambient Temperature | 68 °F 20 °C |
| Average Power, Ambient Temperature | 104 °F 40 °C |
| Average Power, Inner Conductor Temperature | 212 °F 100 °C |
| EN50575 CPR Cable EuroClass Fire Performance | Fca |

Packaging and Weights

| | |
|---------------------|-------------------------|
| Cable weight | 0.15 kg/m 0.101 lb/ft |
|---------------------|-------------------------|

RSJ4-50

Regulatory Compliance/Certifications

Agency

CENELEC

ISO 9001:2015

**Classification**

EN 50575 compliant, Declaration of Performance (DoP) available

Designed, manufactured and/or distributed under this quality management system