# PFU-P-C-0-060-02



### PoE Extender, 2 Port Universal Mount, Outdoor, 2-Port

- Environmentally sealed and tested
- Electrical power management
- Circuit protection electronics
- Optical to electrical Media Conversion
- Automatically conditions electrical voltage to the correct level
- 2 independent PoE ports

Product Classification	
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Product Type	PoE unit
General Specifications	
Data Transfer Rate, maximum	1 Gb
Interface, Input	1GBASE-X (2)
Interface, Output	10/100/1000 BASE-T
Mounting	Universal pole mount   Universal wall mount
Total Ports, quantity	5
Transmission Standards	10/100/1000 BASE-T   1GBASE-X
Input/Output Interface	3 input / 2 output
Dimensions	
Height	224.71 mm   8.847 in
Width	283 mm   11.142 in
Depth	77.02 mm   3.032 in
Electrical Specifications	
Input Voltage Range	-25 to -57 Vdc

# Electrical Performance

Page 1 of 3

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 16, 2022



#### Notes:

- This table provides a partial listing of the maximum supported hybrid cable distances for a range of NEC Class 2 power supply output voltages, hybrid cable copper gauges and extender output power levels.
- NEC Class 2 requires a power supply unit (PSU) limited to less than 60V dc. In practice, some commercial 48V power supplies may be configured to output from 40V up to about 57V.
- Pout is the maximum total PoE extender output power.
- The 1 port and 2 port POE extenders each provide up to 60W of total output power. The 2 port POE extender is limited to 30W per port; whereas the 1 port POE extender can output the full 60W on its single port.

PSU Output Voltage	Cable Gauge (AWG)	Max Cable Length (m) Pout = 60W	Max Cable Length (m) Pout = 45W	Max Cable Length (m) Pout = 30W	Max Cable Length (m) Pout = 15.4W	Max Cable Length (m) Pout = 7W
Maximum	12	888	1301	1886	3131	4633
(57V)	16	351	514	746	1238	1833
Nominal	12	630	922	1335	2217	3280
(48V)	16	249	365	528	877	1297
Minimum (40.5V)	12	448	630	900	1494	2211
	16	177	249	356	591	874

Assumptions:

Hybrid cable ambient temperature: 20°C (Underground/Ducted)
CommScope Cat 6/6A outdoor patch cord length: 50m

CommScope Cat 6/6A outdoor patch cord length: 50m
Patch cord ambient temperature: 55°C (Sunlight Exposed)

# Material Specifications

Finish	Powder coated, off-white
Material Type	Aluminum

## **Environmental Specifications**

Installation temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Note	Not suitable for installation in locations where submersion in water or other liquids is possible (e.g. below grade hand hole or manhole)
Environmental Space	Outdoor
Qualification Standards	CISPR 22/FCC CFR 47   EN300386   ETSI EN 300 019-1-4   IEC 60529, IP68   IEC 60950- 1   IEC 60950-22   IEC 62368   IEEE 802.3at Type 2   NEC Class 2
Safety Standard	CE   CSA   FCC   RCM   SELV   WEEE

### Packaging and Weights

**Weight, net** 5.08 kg | 11.199 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 3

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 16, 2022



# PFU-P-C-0-060-02



Compliant

Page 3 of 3

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 16, 2022

