

# SBJAH4-1D65C-DL



12-port sector antenna, 2x 698–798, 2x 824–896 and 8x 1695–2360 MHz, 65° HPBW, 3x RET and low bands have duplexers

- Interleaved dipole technology providing for attractive, low wind load mechanical package
- Provides support for future Band 14 operations
- The antenna is supplied with mounting kits that provide 0 degree of mechanical downtilt; optional downtilt mounting kits are available

## General Specifications

<b>Antenna Type</b>	Sector
<b>Band</b>	Multiband
<b>Color</b>	Light Gray (RAL 7035)
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Performance Note</b>	Outdoor usage   Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
<b>Radome Material</b>	Fiberglass, UV resistant
<b>Radiator Material</b>	Aluminum   Low loss circuit board
<b>Reflector Material</b>	Aluminum
<b>RF Connector Interface</b>	4.3-10 Female
<b>RF Connector Location</b>	Bottom
<b>RF Connector Quantity, high band</b>	8
<b>RF Connector Quantity, mid band</b>	0
<b>RF Connector Quantity, low band</b>	4
<b>RF Connector Quantity, total</b>	12

## Remote Electrical Tilt (RET) Information


<b>RET Interface</b>	8-pin DIN Female   8-pin DIN Male
<b>RET Interface, quantity</b>	1 female   1 male
<b>Input Voltage</b>	10–30 Vdc
<b>Internal RET</b>	High band (2)   Low band (1)
<b>Power Consumption, idle state, maximum</b>	2 W
<b>Power Consumption, normal conditions, maximum</b>	13 W
<b>Protocol</b>	3GPP/AISG 2.0 (Multi-RET)

# SBJAH4-1D65C-DL

## Dimensions

<b>Width</b>	350 mm   13.78 in
<b>Depth</b>	208 mm   8.189 in
<b>Length</b>	2438 mm   95.984 in
<b>Net Weight, without mounting kit</b>	31.4 kg   69.225 lb

## Array Layout



Array	Freq (MHz)	Conns	RET (MRET)	AISG RET UID
R1	698-798	1-2	1	ANxxxxxxxxxxxxxxxxxxx.1
R2	824-896	3-4		
Y1	1695-2360	5-6	2	ANxxxxxxxxxxxxxxxxxxx.2
Y3	1695-2360	9-10		
Y2	1695-2360	7-8	3	ANxxxxxxxxxxxxxxxxxxx.3
Y4	1695-2360	11-12		

Left Right  
Bottom

(Sizes of colored boxes are not true depictions of array sizes)

## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	1695 – 2360 MHz   698 – 798 MHz   824 – 896 MHz
<b>Polarization</b>	±45°

## Electrical Specifications

Frequency Band, MHz	698–798	824–896	1695–1880	1850–1990	1920–2180	2300–2360
<b>Gain, dBi</b>	15.9	16.4	16.9	17.2	17.6	17.6
<b>Beamwidth, Horizontal, degrees</b>	67	64	63	63	64	65
<b>Beamwidth, Vertical, degrees</b>	9.7	8.6	8.2	7.5	7	6.2
<b>Beam Tilt, degrees</b>	2–11	2–11	2–12	2–12	2–12	2–12
<b>USLS (First Lobe), dB</b>	16	18	17	18	17	14

# SBJAH4-1D65C-DL

<b>Front-to-Back Ratio at 180°, dB</b>	32	34	31	36	36	36
<b>Isolation, Cross Polarization, dB</b>	28	28	28	28	28	28
<b>Isolation, Inter-band, dB</b>	30	30	30	30	30	30
<b>VSWR   Return loss, dB</b>	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
<b>PIM, 3rd Order, 2 x 20 W, dBc</b>	-153	-153	-153	-153	-153	-153
<b>Input Power per Port, maximum, watts</b>	350	350	350	350	350	300

## Mechanical Specifications

<b>Effective Projective Area (EPA), frontal</b>	0.4 m <sup>2</sup>   4.306 ft <sup>2</sup>
<b>Effective Projective Area (EPA), lateral</b>	0.34 m <sup>2</sup>   3.66 ft <sup>2</sup>
<b>Wind Loading @ Velocity, frontal</b>	425.0 N @ 150 km/h (95.5 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, lateral</b>	361.0 N @ 150 km/h (81.2 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, maximum</b>	900.0 N @ 150 km/h (202.3 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, rear</b>	451.0 N @ 150 km/h (101.4 lbf @ 150 km/h)
<b>Wind Speed, maximum</b>	241 km/h (150 mph)

## Packaging and Weights

<b>Width, packed</b>	450 mm   17.717 in
<b>Depth, packed</b>	355 mm   13.976 in
<b>Length, packed</b>	2585 mm   101.772 in
<b>Weight, gross</b>	43.8 kg   96.562 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

BSAMNT-2F	-	Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical
-----------	---	---

# SBJAH4-1D65C-DL


---

tilt applications.

## \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

# BSAMNT-2F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

## Product Classification

**Product Type** Fixed tilt mounting kit

## General Specifications

**Application** Outdoor

**Color** Silver

## Dimensions

**Compatible Diameter, maximum** 115 mm | 4.528 in

**Compatible Diameter, minimum** 60 mm | 2.362 in

**Weight, net** 3.8 kg | 8.378 lb

## Material Specifications

**Material Type** Galvanized steel

## Packaging and Weights

**Included** Brackets | Hardware

**Packaging quantity** 1

**Weight, gross** 4 kg | 8.818 lb

## Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

# BSAMNT-2F

---

