

V360QS-GC3-3XR



2-port small cell antenna, 2x 1695–2690 MHz, 360° HPBW, 3x RET, internal GPS antenna

- Provides a future-ready antenna solution with flexibility to reassign antenna, for example GSM 1800 service to 2.6GHz LTE at a later date
- Employs state-of-the-art ultra wideband technology providing excellent RF performance in all bands
- Excellent RF pattern control over the full operating band and tilt range for desired coverage and interference containment
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

OBSOLETE

This product was discontinued on: March 27, 2020

Replaced By:

V360QS-C3-3XR

2-port small cell antenna, 2x 1695–2690 MHz, 360° HPBW, 1x RET

General Specifications

Antenna Type	Small Cell
Band	Single band
Color	Light Gray (RAL 7035)
GPS Connector Interface	4.3-10 Female
GPS Connector Quantity	1
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Internal GPS frequency band	1,575.42 MHz
Internal GPS VSWR	2
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	2

V360QS-GC3-3XR

RF Connector Quantity, total 2

Remote Electrical Tilt (RET) Information

RET Interface 8-pin DIN Male
RET Interface, quantity 1 male
Input Voltage 10–30 Vdc
Internal RET High band (3)
Power Consumption, idle state, maximum 2 W
Power Consumption, normal conditions, maximum 13 W
Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions

Depth 200 mm | 7.874 in
Length 596 mm | 23.465 in
Net Weight, without mounting kit 7.3 kg | 16.094 lb
Outer Diameter 200 mm | 7.874 in

Electrical Specifications

Impedance 50 ohm
Operating Frequency Band 1695 – 2690 MHz
Polarization $\pm 45^\circ$

Electrical Specifications

Frequency Band, MHz	1695–1880	1850–1990	1920–2200	2300–2500	2500–2690
Gain, dBi	8.9	9.5	9.6	10.1	10.2
Beamwidth, Horizontal, degrees	360	360	360	360	360
Beamwidth, Vertical, degrees	18.4	17.2	16.1	14.4	13.1
Beam Tilt, degrees	0–20	0–20	0–20	0–20	0–20
USLS (First Lobe), dB	16	16	15	15	15
Isolation, Cross Polarization, dB	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-150	-150
Input Power per Port, maximum, watts	100	100	100	100	100

V360QS-GC3-3XR

Electrical Specifications, BASTA

Frequency Band, MHz	1695–1880	1850–1990	1920–2200	2300–2500	2500–2690
Gain by all Beam Tilts, average, dBi	8.4	8.9	9.1	9.6	9.7
Gain by all Beam Tilts Tolerance, dB	±1.2	±0.6	±0.6	±0.8	±0.8
Gain by Beam Tilt, average, dBi	0° 8.3 10° 8.5 20° 8.2	0° 8.9 10° 9.0 20° 8.6	0° 9.2 10° 9.2 20° 8.7	0° 9.6 10° 9.6 20° 9.2	0° 9.7 20° 9.0 10° 10.0
Beamwidth, Vertical Tolerance, degrees	±1.2	±1	±1.3	±1.2	±1.2
USLS, beampeak to 20° above beampeak, dB	15	14	14	14	12

Mechanical Specifications

Wind Loading @ Velocity, frontal	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	58.0 N @ 150 km/h (13.0 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	320 mm 12.598 in
Depth, packed	300 mm 11.811 in
Length, packed	850 mm 33.465 in
Weight, gross	10.1 kg 22.267 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
------------------	---