# VV-65B-R2



4-port sector antenna, 4x 1695–2690 MHz, 65° HPBW, 2x RET. Two pairs of AISG Input and Output ports to separately and independently control the RET on each array for operator sharing applications.

#### **OBSOLETE**

This product was discontinued on: November 30, 2023

Replaced By:

VV-65B-R1 4-port sector antenna, 4x 1695–2690 MHz, 65° HPBW, 1x RET . The two high band arrays utilize a

common tilt.

#### General Specifications

Antenna Type Sector

**Band** Single band

Color Light Gray (RAL 7035)

**Grounding Type** RF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

Radome Material PVC

Reflector Material Aluminum

**RF Connector Interface** 7-16 DIN Female

**RF Connector Location** Bottom

RF Connector Quantity, high band 0
RF Connector Quantity, mid band 4
RF Connector Quantity, low band 0
RF Connector Quantity, total 4

#### Remote Electrical Tilt (RET) Information

**RET Interface** 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 2 female | 2 male

Input Voltage 10-30 Vdc
Internal RET Mid band (2)

ANDREW® an Amphenol company

# VV-65B-R2

Power Consumption, active state, maximum  $$13\ \mathrm{W}$$ 

Power Consumption, idle state, maximum 2 W

**Protocol** 3GPP/AISG 2.0 (Single RET)

**Dimensions** 


 Width
 307 mm | 12.087 in

 Depth
 118 mm | 4.646 in

 Length
 1786 mm | 70.315 in

 Net Weight, antenna only
 13.9 kg | 30.644 lb

# Array Layout



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
Y1	1695-2690	1-2	1	ANxxxxxxxxxxxxx1
Y2	1695-2690	3-4	2	ANxxxxxxxxxxxx2

Left Right Bottom

(Sizes of colored boxes are not true depictions of array sizes)

# Port Configuration



# **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2690 MHz

Polarization ±45°

**Total Input Power, maximum** 400 W @ 50 °C

# **Electrical Specifications**

Frequency Band, MHz	1695-1990	1920-2300	2300-2500	2490-2690
Beamwidth, Horizontal, degrees	66	65	61	57
Beamwidth, Vertical, degrees	5.4	4.8	4.3	4
Beam Tilt, degrees	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	19	18	19	18
Front-to-Back Ratio at 180°, dB	32	36	36	36
Front-to-Back Total Power at 180° ± 30°, dB	25	26	27	26
CPR at Boresight, dB	17	19	22	20
CPR at Sector, dB	10	10	8	9
Isolation, Cross Polarization, dB	30	30	30	30
Isolation, Inter-band, dB	30	30	30	30

ANDREW® an Amphenol company

# VV-65B-R2

VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	
Input Power per Port at 50°C, maximum, watts	300	300	300	300	

## Mechanical Specifications

 Wind Loading @ Velocity, frontal
 696.0 N @ 150 km/h (156.5 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 163.0 N @ 150 km/h (36.6 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

# Packaging and Weights

 Width, packed
 410 mm | 16.142 in

 Depth, packed
 270 mm | 10.63 in

 Length, packed
 1955 mm | 76.969 in

 Weight, gross
 24.5 kg | 54.013 lb

## Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

BSAMNT-3 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



# BSAMNT-3



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

#### Product Classification

**Product Type** Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

**Dimensions** 

Agency

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.2 kg | 13.669 lb

Material Specifications

Material Type Galvanized steel

# Packaging and Weights

Included Brackets | Hardware

Packaging quantity

**Weight, gross** 6.4 kg | 14.11 lb

## Regulatory Compliance/Certifications

Classification

# CE Compliant with the relevant CE product directives CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



