4103904/10 | 2229V WHRL RG6 QD BC 1000



RG 6 Type Quad Shield Plenum Video Coaxial Cable, white jacket, 1000 ft (305 m) reel

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Coaxial video cable

General Specifications

Product Number2229VCable TypeSeries 6Center Conductor TypeSolid

Construction Type Non-armored

Jacket Color White

Dimensions

Cable Length 304.8 m | 1000 ft

Diameter Over Center Conductor Tolerance ±0.0004 in

Diameter Over Center Conductor, specific0.0403 in per 1 strandDiameter Over Dielectric4.318 mm | 0.17 inDiameter Over Inner Shield (Braid)5.131 mm | 0.202 inDiameter Over Jacket, nominal6.604 mm | 0.26 in

Diameter Over Jacket Tolerance ±0.004 in

Diameter Over Outer Shield (Braid)5.893 mm | 0.232 inJacket Thickness0.406 mm | 0.016 inJacket Thickness, minimum spot0.33 mm | 0.013 in

Center Conductor Gauge 18 AWG
Inner Shield (Braid) Gauge 34 AWG
Outer Shield (Braid) Gauge 34 AWG

Electrical Specifications

COMMSCOPE®

4103904/10 | 2229V WHRL RG6 QD BC 1000

Capacitance 50.853 pF/m | 15.5 pF/ft

Characteristic Impedance75 ohmCharacteristic Impedance Tolerance±3 ohm

Conductor dc Resistance 20.997 ohms/km | 6.4 ohms/kft

Dielectric Strength, conductor to shield2500 VdcJacket Spark Test Voltage2500 VacNominal Velocity of Propagation (NVP)84 %

Shield dc Resistance 17.388 ohms/km | 5.3 ohms/kft

Structural Return Loss 15 dB @ 1000-3000 MHz | 20 dB @ 50-1000 MHz | 25 dB @ 5-50MHz

Structural Return Loss Test Method 100% Swept Tested

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
1.0	0.85	0.26
10.0	2.3	0.7
50.0	4.85	1.48
100.0	6.59	2.01
200.0	9.38	2.86
400.0	13.87	4.23
600.0	17.77	5.42
700.0	19.55	5.96
900.0	22.83	6.96
1000.0	24.44	7.45
1450.0	30.64	9.34
2200.0	37.85	11.54
3000.0	42.87	13.07

Material Specifications

Center Conductor MaterialBare copperDielectric MaterialFoam FEPJacket MaterialPVCInner Shield (Braid) Coverage60 %Inner Shield (Braid) MaterialAluminum

Inner Shield (Tape) Material Aluminum/Poly, bonded



4103904/10 | 2229V WHRL RG6 QD BC 1000

Outer Shield (Braid) Coverage 40 %

Outer Shield (Braid) Material Aluminum

Outer Shield (Tape) Material Aluminum/Poly, non-bonded

Mechanical Specifications

Minimum Bend Radius, loaded, times20 timesMinimum Bend Radius, unloaded, times10 times

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental Space Plenum

Temperature Rating, UL 75 °C | 167 °F

Flame Test Method CMP

Safety Standard ETL | cETL

Packaging and Weights

Cable weight 44.645 kg/km | 30 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





