

760102350 | MFC-LCR-16-KYL



LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, simplex multimode, yellow

OBSOLETE

This product was discontinued on: October 10, 2019

Replaced By:

760242154
MFC-LCR-KYL

LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 900um & 1.6 mm fiber, simplex Multimode, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Fiber connector

General Specifications

Body Style

Simplex

Color

Yellow

Ferrule Geometry

Pre-radiused

Interface

LC/UPC

Interface Feature

Keyed

Dimensions

Length

52 mm | 2.047 in

Compatible Cable Diameter

1.6 mm | 0.063 in

Material Specifications

Ferrule Material

Zirconia

Mechanical Specifications

760102350 | MFC-LCR-16-KYL

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode	Multimode
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, typical	0.2 dB
Return Loss, minimum	50 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)