## APS-XT-GPS



#### Antenna Orientation and Location Sensing System

- Available as a retrofit to site-installed CommScope and Third Party antennas
- Monitors Azimuth, Tilt, Roll, Latitude, Longitude and Elevation
- Works with AISG 2.1 controllers as an Alignment Sensor Device and Geographic Location Sensor
- Works with AISG 2.0 controllers in RET emulation mode
- Verify Installations
- Long Term Monitoring
- Additional output port for GPS signal (SMA Female connector type)

#### Product Classification

Product Type RET actuator

General Specifications

AISG Input Connector 8-pin DIN Male

AISG Input Connector Quantity

AISG Output Connector 8-pin DIN Female

AISG Output Connector Quantity

**GPS Output Connector** SMA Female

**GPS Output Connector Quantity** 1

Azimuth Note Accuracy may be affected by installation environment and satellite visibility

±5 m

Azimuth, nominal $\pm 2.5^{\circ}$ ColorGrayElevation $\pm 5 \, \mathrm{m}$ 

 Longitude
 ±5 m

 Roll
 ±1°

 Tilt
 ±1°

Dimensions

Latitude

 Height
 99 mm | 3.898 in

 Width
 325 mm | 12.795 in

 Depth
 166 mm | 6.535 in

**Electrical Specifications** 



### APS-XT-GPS

**GPS Antenna Gain** 31±1 dB @ +25 °C (typical) | 31±4 dB @ -40 °C to +70 °C (typical)

**GPS Frequency Band** 1575.42 ±5 MHz

**GPS Input Voltage, dc** 3.8-5.5 Vdc (dual power supply)

GPS Current, dc ≤ 30 mA
GPS LNA Output 1dB Compression Point ≥0 dBm

**GPS Noise Figure** 1.9 dB typical | 2.5 dB maximum

**GPS Out of Band Rejection** >35 dB @ 1575 ±50 MHz | >50 dB @ 1575 ±100 MHz

**GPS Passband Ripple** ≤1 dB @ 1575.42 ±1.023 MHz, typical | ≤2 dB @ 1575.42 ±5 MHz, typical

Input Voltage 10-30 Vdc

**Boot Time** 15 s

**Boot Time Note** Exceeds AISG 2.0 and 2.1 requirements

Electromagnetic Compatibility (EMC) CFR 47 Part 15, Subpart B, Class A | EN 55022 | EN 55032 | EN 61000-4-

2 | EN 61000-4-3 | EN 61000-4-4 | EN 61000-4-6

Interface Protocol Signal RS-485

**Lightning Surge Capability Test Method** IEC 61000-4-5

**Lightning Surge Capability Waveform** 1.2/50 voltage and 8/20 current combination waveform

**Lightning Surge Test Mode**Common mode

Power Consumption, maximum 3 W

Power Supply AISG (compliant with AISG 2.1 ASD and GLS, exceeds AISG 2.0 RET)

**Protocol** 3GPP/AISG 2.0 compliant

Material Specifications

Material Type ASA

### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Relative Humidity** Up to 95%, non-condensing

Climatic Sequence Test Method IEC 60068-2-14

Cold Exposure Test Method IEC 60068-2-1

Corrosion Test Method IEC 60068-2-11, Test Condition Ka | IEC 60068-2-52, Test Condition Kb

**Damp Heat Exposure Test Method**IEC 60068-2-30, Test Condition Db

**Heat Exposure Test Method** IEC 60068-2-2

**Ingress Protection Test Method**IEC 60529:2001, IP56

Page 2 of 3



# APS-XT-GPS

Packaged Product Shock Test MethodASTM D4169GR-63-CORE, Section 4.1.1

**Rain Simulation Test Method** IEC 60068-2-18, Test Condition Ra, Method 1

**UV Resistance Test Method** IEC 60068-2-5, Test Condition B

Vibration Test Method ASTM D4169 | IEC 60068-2-6

Packaging and Weights

**Weight, net** 1.5 kg | 3.307 lb

### Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

