

Product Classification

#### Diplexer, 380–960 MHz/1695–2690 MHz,dc Sense,4.3-10

- BTS-to-feeder and feeder-to-antenna application
- New 4.3-10 connectors for improved PIM performance and size reduction
- Automatic dc switching with dc sense
- Convertible mounting brackets

Product Type	Diplexer
General Specifications	
Product Family	CBC426
Color	Gray
Common Port Label	ANT
Modularity	1-Single
Mounting	Pole   Wall
Mounting Pipe Hardware	Band clamps (2)
RF Connector Interface	4.3-10 Female
RF Connector Interface Body Style	Long neck
Dimensions	
Height	152 mm   5.984 in
Width	121 mm   4.764 in
Depth	56.5 mm   2.224 in
Ground Screw Diameter	6 mm   0.236 in

Mounting Pipe Diameter Range


Page 1 of 5


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024


40-160 mm



### Outline Drawing







### **Electrical Specifications**

#### Impedance

50 ohm

License Band, Band Pass

 APT 700
 |
 AWS 1700
 |
 CEL 900
 |
 DCS 1800
 |
 EDD 800
 |
 IMT

 2100
 |
 IMT 2600
 |
 LMR 750
 |
 LMR 800
 |
 LMR 900
 |
 PCS 1900
 |
 TDD

 1900
 |
 TDD 2000
 |
 TDD 2300
 |
 TDD 2600
 |
 USA 600
 |
 USA 700
 |
 USA 750
 |
 WCS 2300

### Electrical Specifications, Common Port

Composite Power, RMS 250 W

#### Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through Method

Auto sensing

Page 2 of 5



dc/AISG Pass-through Path	See logic table
Lightning Surge Current	10 kA
Lightning Surge Current Waveform	8/20 waveform
Voltage	7-30 Vdc

### Electrical Specifications, AISG

AISG Carrier	2176 KHz ± 100 ppm
Insertion Loss, maximum	1 dB
Return Loss, minimum	15 dB

### **Electrical Specifications**


Sub-module	1	1
Branch	1	2
Port Designation	380-960	1695-2690
License Band	LMR 750, Band Pass LMR 800, Band Pass USA 700, Band Pass USA 750, Band Pass USA 600, Band Pass CEL 850, Band Pass	PCS 1900, Band Pass WCS 2300, Band Pass AWS 1700, Band Pass TDD 2600, Band Pass

### Electrical Specifications, Band Pass

Frequency Range, MHz	380-960	1695-2690
Insertion Loss, typical, dB	0.1	0.1
Total Group Delay, typical, ns	2	4
Return Loss, typical, dB	24	22
Isolation, typical, dB	65	63
Input Power, RMS, maximum, W	200	200
Input Power, PEP, maximum, W	2000	2000
3rd Order PIM, minimum, dBc	-161	-161
3rd Order PIM Test Method	2 x 20 W CW tones	2 x 20 W CW tones

### Block Diagram





Page 4 of 5



### Logic Table

Combining N	lode Operation (G	round Based)	
RF P	orts Input DC Vol	tage	
380 to 960 MHz	1695 to 2690 MHz	COMMON	DC/AISG Path Selection
7 ≤ V ≤ 30	<7	<7	380 to 960 MHz to COMMON "ON"
<7	7 ≤ V ≤ 30	<7	1695 to 2690 MHz to COMMON "ON"
7 ≤ V ≤ 30	7 ≤ V ≤ 30	<7	1695 to 2690 MHz to COMMON "ON"

Splitting N	/lode Operation (T	ower Top)	
RF Ports In	pedance DC (Loa	ad sensing)	
380 to 960 MHz	1695 to 2690 MHz	COMMON	DC/AISG Path Selection
open/load	short	7≤V≤30	COMMON to 380-960 "ON"
short	open/load	7≤V≤30	COMMON to 1695-2690 "ON"
open/load	open/load	7≤V≤30	ALL ports ON
short	short	7≤V≤30	ALL ports OFF

### Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%-100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67
Packaging and Weights	
Included	Manuatian bandunara

Included	Mounting hardware
Mounting Hardware Weight	0.6 kg   1.323 lb
Volume	1 L
Weight, without mounting hardware	1.6 kg   3.527 lb

#### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 5 of 5

