

Power Distribution Unit, multimode for single and dual band tower mounted amplifiers (TMAs)

Product Classification

Product Type Power distribution unit

General Specifications

ApplicationIndoorColorLight gray

 LED Indicators, green
 Normal
 Power supply

 LED Indicators, red
 Alarm
 dc/dc Converter

Modules per Unit, quantity

 Output Control
 6-position DIP switch

 Output Interface
 9-pin D-sub Female

Output Ports per Module, quantity 6

Dimensions


 Height
 44 mm | 1.732 in

 Width
 483 mm | 19.016 in

 Depth
 130 mm | 5.118 in



Outline Drawing



Electrical Specifications

Input Lightning Surge Current 1 kA

Input Lightning Surge Current Waveform 8/20 waveform

Input Overcurrent Protection Internal slow blow fuse

Input Voltage, operational20-60 VdcOutput Current per Port, maximum400 mA

Output Current, maximum 2.2 A
Output Lightning Surge Current 2 kA

Output Lightning Surge Current Waveform 8/20 waveform

Output Overcurrent Protection Hiccup mode current limiting

Output Voltage Ripple, maximum 100 mVpp

Output Voltage, typical 12 V

Alarm Control 6-position DIP switch

Alarm Current Range, high setting 175–312 mA

Alarm Current Range, low setting 20–163 mA

Alarm Interface 9-pin D-sub Female

Alarm Relays Normally closed | Normally open

Electrical Safety Standard CE | EN 60950

Power Consumption, maximum 40 W

COMMSCOPE®

Power Supply Control


Power Supply Interface

Toggle switch

4-pin single row header Male



Block Diagram



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Ingress Protection Test Method IEC 60529:2001, IP20

Packaging and Weights

Weight, net 1.1 kg | 2.425 lb