
# 760249370 | N-004-DS-8Z-MSUYL/093



Fiber indoor cable, Low Smoke Zero Halogen Distribution, 4 fiber single-unit, Singlemode G.657.A1, Meters jacket marking, Yellow jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-DS

## General Specifications

Cable TypeDistributionConstruction TypeNon-armored

Subunit TypeGel-freeJacket ColorYellowJacket MarkingMeters

Total Fiber Count 4


**Dimensions** 

**Diameter Over Jacket** 4.8 mm | 0.189 in

## Representative Image



#### 760249370 N-004-DS-8Z-MSUYL/093



## Mechanical Specifications

Minimum Bend Radius, loaded 96 mm | 3.78 in Minimum Bend Radius, unloaded 48 mm | 1.89 in Tensile Load, long term, maximum 198 N | 44.512 lbf 660 N | 148.374 lbf Tensile Load, short term, maximum 10 N/mm | 57.101 lb/in

IEC 60794-1 E3 **Compression Test Method** 

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1 E1

**Twist** 10 cycles

**Twist Test Method** IEC 60794-1 E7

**Optical Specifications** 

Compression

**Fiber Type** G.657.A1

## Optical Specifications, Wavelength Specific

0.30 dB/km @ 1,550 nm | 0.40 dB/km @ 1,310 nm Attenuation, maximum

## **Environmental Specifications**

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F) -20 °C to +70 °C (-4 °F to +158 °F) **Operating Temperature** 

Page 2 of 3



## 760249370 | N-004-DS-8Z-MSUYL/093

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Environmental Space** Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR (UL) and c(UL)

**Flame Test Method** IEC 60332-3 | UL 1666 | UL 1685

## **Environmental Test Specifications**

**Temperature Cycle Test Method** IEC 60794-1 F1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-8Z-TB-0.40/0.30/093 - Low Water Peak, Dispersion-Unshifted Singlemode Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

