

# CPC2282

## Base Product



GigaSPEED XL® MGS400 to MGS400 on 1071 Solid Cable Pre-terminated Cord

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Brand</b>	GigaSPEED XL®
<b>Product Series</b>	CPC
<b>Ordering Note</b>	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Solid
<b>Information Outlet Color</b>	Black   Blue   Gray   Green   Ivory   Orange   Red   White   Yellow
<b>Interface, Connector A</b>	Information outlet
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	Information outlet
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	Black   Blue   Dark gray   Light blue   Lilac   Orange   Red   Slate   Spring green   White   Yellow
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	IEEE 802.3bt Type 4
<b>Wiring</b>	T568B

# CPC2282

---

## Dimensions

<b>Cable Assembly Length Range (m)</b>	1 – 100
<b>Cable Assembly Length Range (ft)</b>	1 – 328
<b>Diameter Over Jacket</b>	5.89 mm   0.232 in
<b>Compatible Conductor Gauge, solid</b>	23 AWG

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Electrical Specifications

<b>dc Resistance, maximum</b>	0.3 ohm
<b>Safety Voltage Rating</b>	300 V

## Ordering Tree

# CPC2282

CPC     - <sup>9</sup> <sup>10</sup> <sup>11</sup> <sup>12</sup>

## Outlet Color

9	0	Not applicable
	1	Black
	2	Blue
	3	Gray
	4	Green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac

## Jacket Color

10	1	Black
	2	Light blue
	3	Dark gray
	4	Spring green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac
	C	Gray
	K	Pink
	L	Violet
	M	Green
	Z	Blue

## UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

## Length

12	XXX
----	-----

## Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Material Specifications

<b>Contact Plating Material</b>	Precious metals
<b>Material Type</b>	Copper alloy   Polycarbonate

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
<b>Plug Retention Force, minimum</b>	133 N   29.9 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Environmental Space</b>	Non-plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ETL   cETL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system