

NCC44FZJB



NCC Cat 6A F/UTP, LSZH, Plug-to-SLX Jack, (Black), Class Dca

Product Classification

| | |
|------------------------------|---|
| Regional Availability | India |
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |
| Product Series | NCC |
| Ordering Note | Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices |

General Specifications

| | |
|---------------------------------------|----------------------|
| ANSI/TIA Category | 6A |
| Cable Type | F/UTP (shielded) |
| Conductor Type | Solid |
| Information Outlet Color | Black Gray White |
| Interface, Connector A | Shielded, .310 Plug |
| Interface Feature, connector A | Standard |
| Interface, Connector B | AMP-TWIST SLX,6AS |
| Interface Feature, connector B | Standard |
| Jacket Color | White |
| Pairs, quantity | 4 |
| Transmission Standards | IEEE 802.3bt Type 4 |
| Wiring | T568B |

Dimensions

NCC44FZJB

| | |
|--|--------------------|
| Cable Assembly Length Range (m) | 1 – 100 |
| Cable Assembly Length Range (ft) | 1 – 328 |
| Diameter Over Jacket | 7.52 mm 0.296 in |
| Compatible Conductor Gauge, solid | 23 AWG |

Ordering Tree

NCC - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

| | | |
|---|-------|----------------|
| 9 | 0 | Not applicable |
| | 1 | Black |
| | 2 | Blue |
| | 3 | Gray |
| | 4 | Green |
| | 5 | Ivory |
| | 6 | Orange |
| | 7 | Red |
| | 8 | White |
| | 9 | Yellow |
| B | Lilac | |

Jacket Color

| | | |
|----|--------|--------------|
| 10 | 1 | Black |
| | 2 | Light blue |
| | 3 | Dark gray |
| | 4 | Spring green |
| | 5 | Ivory |
| | 6 | Orange |
| | 7 | Red |
| | 8 | White |
| | 9 | Yellow |
| | B | Lilac |
| C | Gray | |
| K | Pink | |
| L | Violet | |
| M | Green | |
| Z | Blue | |

UOM

| | | |
|----|---|-------|
| 11 | M | Meter |
|----|---|-------|

Length

| | |
|----|-----|
| 12 | XXX |
|----|-----|

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

| | |
|---------------------------------|------------------|
| Conductor Material | Phosphor Bronze |
| Contact Plating Material | Gold over nickel |

Mechanical Specifications

| | |
|-------------------------------------|-----------|
| Plug Insertion Life, minimum | 750 times |
|-------------------------------------|-----------|

Environmental Specifications

| | |
|---|-------------------------------------|
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| EN50575 CPR Cable EuroClass Fire Performance | Dca |
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Safety Standard | UL 1863 |

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CENELEC

EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant/Exempted

