
760249748 | C-048-LA-5Y-M12BK/22G/093



Fiber indoor/outdoor cable, loose tube gel-filled CST, 48 fiber, Multimode OM3, Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LA
General Specifications	
Cable Type	Stranded loose tube
Construction Type	Armored
Fiber Type, quantity	48
Fibers per Subunit, quantity	12
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-filled
Total Fiber Count	48
Dimensions	
Buffer Tube/Subunit Diameter	2.2 mm 0.087 in
Diameter Over Jacket	12.3 mm 0.484 in


Representative Image

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 3, 2023



760249748 | C-048-LA-5Y-M12BK/22G/093



Mechanical Specifications

Minimum Bend Radius, loaded	246 mm 9.685 in
Minimum Bend Radius, unloaded	123 mm 4.843 in
Tensile Load, short term, maximum	2000 N 449.618 lbf
Compression	15 N/mm 85.652 lb/in
Compression Test Method	IEC 60794-1-2 E3
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum

Fiber Type

1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature	-10 °C to +50 °C (+14 °F to +122 °F)
Operating Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Buried Ducted Indoor/Outdoor Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60332-1 IEC 60332-3-24 IEC 60754-2 IEC 61034-2
Water Penentration	24 h
Water Penentration Test Method	IEC 60794-1 F5B

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 3, 2023



760249748 | C-048-LA-5Y-M12BK/22G/093

Environmental Test Specifications

Temperature Cycle-30 °C to +70 °C (-22 °F to +158 °F)Temperature Cycle Test MethodIEC 60794-1-2 F1Packaging and Weights171 kg/km | 114.907 lb/kftCable weight171 kg/km | 114.907 lb/kftRegulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 3, 2023

