



ConQuest® Empty Conduit, 2 in, SDR 13.5, orange, with pull tape

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Orange
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	762 m 2500 ft
Inner Diameter, nominal	50.876 mm 2.003 in
Outer Diameter, nominal	60.325 mm 2.375 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	4.47 mm 0.176 in
Nominal Size	2 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE) Polyester
Melt Flow Rate Test Method	ASTM D1238

CX3799861 | 2000135WP1250TAPE COEX

Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 660.4 mm | 26 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Breaking Strength 566.99 kg | 1250 lb

Pull Line Type Tape

Pulling Tension, maximum 1,170.268 kg | 2580 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 791.703 kg/km | 532 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance