


# 760250293 | P-004-DS-HY-5K-F29AQ/4X12AWG



LazrSPEED® Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 12 AWG, OM4 Bend Insensitive

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, copper and fiber
<b>Product Brand</b>	LazrSPEED®

## General Specifications

<b>Cable Type</b>	Distribution   Hybrid   Stranded indoor
<b>Conductor Type, singles</b>	Stranded
<b>Conductors, quantity</b>	4
<b>Construction Type</b>	Non-armored
<b>Fiber Short Description</b>	P-001-SP29
<b>Subunit Type</b>	Gel-free
<b>Filler, quantity</b>	0
<b>Jacket Color</b>	Aqua
<b>Subunit Jacket Color</b>	Aqua
<b>Subunit, quantity</b>	4
<b>Fibers per Subunit, quantity</b>	1
<b>Total Fiber Count</b>	4

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.794 mm   0.11 in
<b>Diameter Over Jacket</b>	12.192 mm   0.48 in


# 760250293 | P-004-DS-HY-5K-F29AQ/4X12AWG

**Conductor Gauge** 12 AWG

## Electrical Specifications

**Conductor dc Resistance** 5.413 ohms/km | 1.65 ohms/kft

## Representative Image



## Material Specifications

**Conductor Material** Bare copper | Stranded copper wire

**Insulation Material, singles** PVC

**Jacket Material** Fire retardant PVC

**Ripcord Material** Polyester

## Mechanical Specifications

**Minimum Bend Radius, loaded** 181.61 mm | 7.15 in

**Minimum Bend Radius, unloaded** 120.904 mm | 4.76 in

# 760250293 | P-004-DS-HY-5K-F29AQ/4X12AWG

<b>Tensile Load, long term, maximum</b>	467.063 N   105 lbf
<b>Tensile Load, short term, maximum</b>	1,552.429 N   349 lbf
<b>Compression</b>	1.018 kg/mm   57 lb/in
<b>Compression Test Method</b>	FOTP-41
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	FOTP-104
<b>Impact</b>	2.17 ft lb   2.942 N-m
<b>Impact Test Method</b>	FOTP-25
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	FOTP-33
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85
<b>Vertical Rise, maximum</b>	171.42 m   562.4 ft

## Optical Specifications

<b>Fiber Type</b>	OM4, LazrSPEED®   OM4, bend insensitive
-------------------	---

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +70 °C (-32 °F to +158 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-83-596   Telcordia GR-409   UL 13   UL 444
<b>Environmental Space</b>	Plenum   Wireless installation
<b>Flame Test Listing</b>	NEC CL3P-OF (ETL) and c(ETL)   NEC CMP-OF (ETL) and c(ETL)
<b>Flame Test Method</b>	NFPA 262

## Environmental Test Specifications

<b>Low High Bend</b>	0 °C to +70 °C (+32 °F to +158 °F)
<b>Low High Bend Test Method</b>	FOTP-37
<b>Temperature Cycle</b>	0 °C to +70 °C (+32 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	FOTP-3

## Packaging and Weights

# 760250293 | P-004-DS-HY-5K-F29AQ/4X12AWG

---

**Cable weight**

277.84 kg/km | 186.7 lb/kft

## Included Products

CS-5K-TB – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable