

#### Standard Grounding Kit for elliptical waveguide 43

Product Classification	
Product Type	Grounding kit
Ordering Note	CommScope® non-standard product
General Specifications	
Bonding Conductor Jacketing Material	PVC
Bonding Conductor Material	Copper
Cable Type	Elliptical waveguide
Color	Black
Grounding Kit Type	Standard Grounding Kits
Grounding Strap Material	Copper
Lug Attachment	Factory attached
Lug Туре	One-hole lug, screw on
Thread Size	3/8 in
Dimensions	

Bonding Conductor Length	609.6 mm   24 in
Cable Jacketing Removal Length, maximum	58.42 mm   2.3 in
Cable Jacketing Removal Length, minimum	55.88 mm   2.2 in
Compatible Diameter, maximum	50.8 mm   2 in
Compatible Diameter, minimum	49.022 mm   1.93 in
Waveguide Size	WR187   WG12   R48

### **Electrical Specifications**

**Current Handling** 

Tested to withstand 130,000 amps peak current surge

Page 1 of 5

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 15, 2023



Current Handling Test Method	MIL-STD-1757
Grounding, Bonding and Shielding Test Method	MIL-STD-188-124A
Lightning Protection Test Method	IEC 1024-1
Material Specifications	
Rivet Material	Copper
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Blowing Rain Test Method	MIL-STD-810, Method 506
Corrosion Test Method	MIL-STD-1344, Method 1001
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521
Humidity Test Method	MIL-STD-1344, Method 1002
Immersion Test Method	IEC 60529:2001, IP68
UV Resistance Test Method	MIL-STD-810, Method 505
Vibration Test Method	MIL-STD-202, Method 214
Weatherproofing Method	Butyl and electric tape
Packaging and Weights	
Height, packed	266.7 mm   10.5 in
Width, packed	266.7 mm   10.5 in
Length, packed	58.42 mm   2.3 in
Included	Grounding kit   Hardware   Lug   One roll of 2 in PVC tape   One roll of 24 in butyl rubber tape
Packaging quantity	1
Weight, gross	0.64 kg   1.411 lb
Regulatory Compliance/Certifications	

# AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant

Page 2 of 5

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 15, 2023



UK-ROHS

e

Compliant

#### Included Products

**ISO** 9001:2015

9905-71 – Black 2 in PVC Tape, 20 ft

#### \* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02

Page 3 of 5

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 15, 2023





#### Black 2 in PVC Tape, 20 ft

Product Classification		
Product Type	Weatherproofing tape	
Ordering Note	CommScope® non-standard product	
General Specifications		
Application	Provides additional moisture seal for cable connections	
Applications per Kit	Four 1/2 in-1/2 in   Four 1/2 in-7/8 in to device   One 1/2 in-2-1/4 in   Two 1/2 in-7/8 in	
Color	Black	
Dimensions		
Width	50.8 mm   2 in	
Length	6096 mm   240 in	
Nominal Size	1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in	
Material Specifications		
Material Type	PVC tape	
Environmental Specifications		
UV Resistance Test Method	PVC tape test method UL 510, ASTM D1000	
Weather Resistance Test Method	04AS00-03.6.0   MIL-STD-1344A, Method 1002	
Packaging and Weights		
Height, packed	63.5 mm   2.5 in	
Width, packed	63.5 mm   2.5 in	
Length, packed	50.8 mm   2 in	

Page 4 of 5

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 13, 2023



**Packaging quantity** 

Weight, gross

1

0.08 kg | 0.176 lb

### Regulatory Compliance/Certifications

#### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Agency

Page 5 of 5

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 13, 2023

