Type N Male for CNT-300 braided cable



Product Classification

Product Type Braided cable connector

Product Brand CNT®

General Specifications

Body Style Straight

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

Interface N Male

Outer Contact Attachment Method Crimp

Outer Contact Plating Trimetal

Pressurizable No

Dimensions

Width 20.25 mm | 0.797 in


Length 41.5 mm | 1.634 in

Diameter 20.25 mm | 0.797 in

Nominal Size 0.300 in

Outline Drawing





Electrical Specifications

Insertion Loss, typical 0.05 dB

Average Power at Frequency 360.0 W @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage2000 VInner Contact Resistance, maximum1 mOhm

Insulation Resistance, minimum5000 MOhmOperating Frequency Band0 - 6000 MHz

Outer Contact Resistance, maximum 0.25 m0hm

Peak Power, maximum 10 kW RF Operating Voltage, maximum (vrms) 707 V

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

0–3000 MHz 1.065 30.05 **3000–6000 MHz** 1.222 20.01

Mechanical Specifications

Connector Retention Tensile Force 220 N | 49.458 lbf

Page 2 of 4



Connector Retention Torque0.45 N-m | 3.983 in lbCoupling Nut Proof Torque1.7 N-m | 15.046 in lbCoupling Nut Proof Torque MethodIEC 61169-16:9.3.6Coupling Nut Retention Force450 N | 101.164 lbfCoupling Nut Retention Force MethodIEC 61169-16:9.3.11

Insertion Force 28 N | 6.295 lbf

Insertion Force Method IEC 61169-16:9.3.5

Interface Durability 500 cycles

Interface Durability MethodIEC 61169-16:9.5Mechanical Shock Test MethodIEC 60068-2-27

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Immersion Depth 1 m
Immersion Test Mating Mated

Immersion Test Method IEC 60529:2001, IP68

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 28.91 g | 0.064 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant



* Footnotes

Insertion Loss, typical 0.05v⁻freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours

