BC-40-16D



• •

Pipe-to-Pipe Clamp, joins two 4 in to 9 in OD round members

Product Classification	
Product Type	Clamp set
General Specifications	
Mounting	Pipe-to-pipe
Tower Taper	Non-tapered Tapered
Dimensions	
Height	152.4 mm 6 in
Width	304.8 mm 12 in
Length	406.4 mm 16 in
Mounting Diameter 2, maximum	228.6 mm 9 in
Mounting Diameter 2, minimum	101.6 mm 4 in
Mounting Diameter, maximum	228.6 mm 9 in
Mounting Diameter, minimum	101.6 mm 4 in
Material Specifications	

Material	Туре
material	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,

Hot dip galvanized steel

Packaging and Weights

Included	Clamp halves Threaded rod
Packaging quantity	2
Weight, net	31.5 kg 69.446 lb

Page 1 of 1

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 18, 2023

