# BC-40-16



Pipe-to-Pipe Clamp, heavy duty, joins two 4 in to 9 in OD round members

### **Product Classification**

Product Type Clamp set

#### General Specifications

MountingPipe-to-pipeTower TaperTapered

#### **Dimensions**

 Height
 50.8 mm | 2 in

 Width
 304.8 mm | 12 in

 Length
 406.4 mm | 16 in

 Mounting Diameter, maximum
 228.6 mm | 9 in

 Mounting Diameter, minimum
 101.6 mm | 4 in

## Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

**Weight, net** 16.3 kg | 35.935 lb

### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



