

124553-000 | OCC1C-F-471-S2SEC-2T-U41

OCC1C compact CWDM, 8 channels + 1310 nm port, single demux, 1471 nm starting wavelength, SC/APC, 0.9 mm cable



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	CWDM component
Product Series	OCC1C

General Specifications

Device Type	Component, rectangular
Functionality	Demultiplexing
Technology Type	Free space optics
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, Input	SC
Interface Feature, Input	APC
Interface, Output	SC
Interface Feature, Output	APC
Multiplexers, quantity	1
Port Type, optional	1310 nm port Tx and Rx test fibers

Dimensions

Pigtail length, input	2.5 m 8.202 ft
Pigtail length, output	2.5 m 8.202 ft
Pigtail Diameter	0.9 mm 0.035 in

Optical Specifications

124553-000 | OCC1C-F-471-S2SEC-2T-U41

Channel Spacing 20 nm
Starting Wavelength 1471 nm

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance