CSG78-12B2U



SureGround® Universal Compact Grounding Kit for 7/8 in corrugated and smoothwall coaxial cable

Product Classification

Product TypeGrounding kitProduct BrandSureGround®

Ordering Note CommScope® standard product (Global)

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Smoothwall

Color Black

Grounding Kit TypeCompact SureGround® Grounding Kits

Grounding Strap MaterialTinned copperLug AttachmentField attachedLug TypeTwo-hole lug

Thread Size 3/8 in

Dimensions

 Enclosure Width
 40.64 mm | 1.6 in

 Bonding Conductor Length
 1143 mm | 45 in

 Enclosure Length
 63.5 mm | 2.5 in

Compatible Diameter, maximum28.372 mm1.117 inCompatible Diameter, minimum27.559 mm1.085 in

Nominal Size 7/8 in

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

COMMSCOPE®

CSG78-12B2U

Grounding, Bonding and Shielding Test MethodMIL-STD-188-124A

Lightning Protection Test Method IEC 1024-1

Material Specifications

Locking Bail MaterialStainless steelRivet MaterialTinned copper

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +176 \,^{\circ}\text{F)}$

Blowing Rain Test Method MIL-STD-810, Method 506

Corrosion Test Method MIL-STD-1344, Method 1001

Freezing Rain/Icing Test Method MIL-STD-810, Method 521

Humidity Test Method MIL-STD-1344, Method 1002

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505

Vibration Test Method MIL-STD-202, Method 214

Weatherproofing Method Tinned copper strap contact overmolded with EPDM rubber

Packaging and Weights

 Height, packed
 447.04 mm | 17.6 in

 Width, packed
 396.24 mm | 15.6 in

 Length, packed
 68.58 mm | 2.7 in

Included Grounding kit | Hardware | Lug

Packaging quantity 1

Weight, gross 0.45 kg | 0.992 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



CSG78-12B2U



* Footnotes

Grounding, Bonding and Shielding Test MethodMilitary Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test MethodProtection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

