

# HSG-FSJ4-MD



HELIAX® SureGuard® Boot for 4.3-10 and 4.1-9.5 jumpers to antennas or devices

## OBSOLETE

This product was discontinued on: October 16, 2019

### Replaced By:

HSG-FSJ4-SMALL

HELIAX® SureGuard® Boot for 1/2 in right angle 4.3-10 and 4.1-9.5 jumpers to antennas or devices

## Product Classification

<b>Product Type</b>	Weatherproofing boot
<b>Product Brand</b>	HELIAX®   SureGuard®
<b>Ordering Note</b>	CommScope® non-standard product   Not sold separately— sold exclusively with HELIAX® SureGuard jumpers

## General Specifications

<b>Application</b>	Provides additional moisture seal for cable connections
<b>Applications per Kit</b>	One 1/2 in to antenna or device connection
<b>Color</b>	Black

## Dimensions

<b>Width</b>	55 mm   2.165 in
<b>Length</b>	95 mm   3.74 in
<b>Cable Diameter for Seal, maximum</b>	13.74 mm   0.541 in
<b>Cable Diameter for Seal, minimum</b>	13.18 mm   0.519 in
<b>Inner Diameter</b>	11.3 mm   0.445 in
<b>Nominal Size</b>	1/2 in

## Material Specifications

<b>Material Type</b>	Silicone rubber
----------------------	-----------------

# HSG-FSJ4-MD

---

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>UV Resistance Test Method</b>	ASTM G154-12a
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	IEC 60068-2-11   IEC 60529:2001, IP68

## Packaging and Weights

<b>Height, packed</b>	41 mm   1.614 in
<b>Width, packed</b>	120 mm   4.724 in
<b>Length, packed</b>	140 mm   5.512 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	19.2 g   0.042 lb