

CPC5482

Base Product



GigaSPEED XL® VisiPatch® Single-ended 4-pair Solid Patch Cord

This product will be discontinued on: July 1, 2024

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED XL® VisiPatch®
Product Series	CPC
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	VisiPatch®
Interface Feature, connector A	Standard
Interface, Connector B	Unterminated
Interface Feature, connector B	Standard
Jacket Color	Black Blue Dark gray Light blue Lilac Orange Red Slate Spring green White Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4

CPC5482

Wiring VisiPatch®

Dimensions

Cable Assembly Length Range (m) 1 – 30
Cable Assembly Length Range (ft) 1 – 100
Diameter Over Jacket 5.89 mm | 0.232 in
Compatible Conductor Gauge, solid 23 AWG

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3	White/Orange	
Position 4	Orange	
Position 5	Lt. Green	
Position 6	Green	
Position 7	Lt. Brown	
Position 8	Brown	

Electrical Specifications

dc Resistance, maximum 0.3 ohm

Ordering Tree

CPC5482

CPC - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

9	0	Not applicable
	1	Black
	2	Blue
	3	Gray
	4	Green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac

Jacket Color

10	1	Black
	2	Light blue
	3	Dark gray
	4	Spring green
	5	Ivory
	6	Orange
	7	Red
	8	White
	9	Yellow
	B	Lilac
	C	Gray
	K	Pink
	L	Violet
	M	Green
	Z	Blue

UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

Length

12

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N 9.892 lbf

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Safety Standard	ETL cETL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system