


# MLOC-5-FIXM-HM-2M



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 male, size 1/4", length 2 meters

## Product Classification

<b>Product Type</b>	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	MLOC

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	M-LOC Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	2 m   6.562 ft
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-119 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000–3000 MHz	1.07	30	0.82
3000–4200 MHz	1.11	26	0.99

# MLOC-5-FIXM-HM-2M

---

4200–5000 MHz                      1.12                      25                      1.09

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends**                      25.4 mm | 1 in

**Minimum Bend Radius, single Bend**                      25.4 mm | 1 in

## Environmental Specifications

**Installation temperature**                      -40 °C to +60 °C (-40 °F to +140 °F)

**Operating Temperature**                      -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature**                      -55 °C to +85 °C (-67 °F to +185 °F)

**Immersion Test Method**                      Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ROHS

### Classification

Above maximum concentration value

Compliant/Exempted

