FJ-3S30U1H0J



HELIAX® Discrete ruggedized Bi-Di Drop cable assembly, 3 Single Mode fiber, SLC to HMFOC, LSZH cable, staggered breakout for conduit pulls

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product TypeWireless Fiber Cable Assemblies

Product Brand HELIAX®

General Specifications

Construction Type Discrete fiber tail

Interface, Connector A LC

 Interface Body Style, connector A
 Straight

 Interface, Connector B
 HMFOC

 Interface Feature, connector B
 Outdoor

 Interface Body Style, connector B
 Straight

 Jacket Color
 Black

Total Fibers, quantity 3

Dimensions


Cable Assembly Length Range (m) 4 - 50

Diameter Over Jacket 5.4 mm | 0.213 in

Ordering Tree



FJ-3S30U1H0J



Optical Specifications

Fiber Type G.657.A2/B2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Indoor | Outdoor

Packaging and Weights

Cable weight 29 kg/km | 19.487 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

FJ-3S30U1H0J

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

