

# CX3199949 | 075G135PP200ROPE-5K' CX



ConQuest® Empty Conduit, 3/4 in, SDR 13.5, gray, with pull rope

## Product Classification

<b>Product Type</b>	Empty conduit
<b>Product Brand</b>	ConQuest®

## General Specifications

<b>Color</b>	Gray
<b>Conduit Type</b>	Non-toneable
<b>Density Test Method</b>	ASTM D792A
<b>Density, maximum</b>	0.955 g/cm <sup>3</sup>   0.035 lb/in <sup>3</sup>
<b>Density, minimum</b>	0.941 g/cm <sup>3</sup>   0.034 lb/in <sup>3</sup>
<b>Design Standard</b>	ASTM D3350-05
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	1524 m   5000 ft
<b>Inner Diameter, nominal</b>	22.2 mm   0.874 in
<b>Outer Diameter, nominal</b>	26.67 mm   1.05 in
<b>Wall Thickness Designation</b>	SDR 13.5
<b>Wall Thickness, minimum</b>	1.981 mm   0.078 in
<b>Nominal Size</b>	3/4 in

## Material Specifications

<b>Flexural Modulus, minimum</b>	551.581 N/mm <sup>2</sup>   80000 psi
<b>Flexural Property Test Method</b>	ASTM D790
<b>Hydrostatic Design Basis</b>	Not pressure rated
<b>Hydrostatic Design Test Method</b>	ASTM D2837
<b>Material Type</b>	High density polyethylene (HDPE)   Polypropylene
<b>Melt Flow Rate Test Method</b>	ASTM D1238

# CX3199949 | 075G135PP200ROPE-5K' CX

---

**Melt Flow Rate, maximum** 0.39 g/10 min

## Mechanical Specifications

**Minimum Bend Radius, unsupported** 304.8 mm | 12 in

**Tensile Property Test Method** ASTM D638

**Tensile Strength at yield, minimum** 20.684 N/mm<sup>2</sup> | 3000 psi

**Breaking Strength** 90.718 kg | 200 lb

**Pull Line Type** Rope

**Pulling Tension, maximum** 229.064 kg | 505 lb

## Environmental Specifications

**Environmental Stress Crack Resistance** Failure rate of 10% within 96 hours

**Environmental Stress Test Method** ASTM D1693, ESCR Condition B

## Packaging and Weights

**Weight, net** 165.186 kg/km | 111 lb/kft

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Environmental Stress Crack Resistance** ESCR—Environmental Stress Crack Resistance