



ConQuest® Empty Conduit, 1 in, SDR 13.5, terracotta, with pull tape

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Empty conduit
Product Brand	ConQuest®
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm³ 0.035 lb/in³
Density, minimum	0.941 g/cm³ 0.034 lb/in³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	914.4 m 3000 ft
Inner Diameter, nominal	27.965 mm 1.101 in
Outer Diameter, nominal	33.401 mm 1.315 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	2.464 mm 0.097 in
Nominal Size	1 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm² 80000 psi
Flexural Property Test Method	ASTM D790

CX3299986 | 100T135WP1250TAPE COEX

Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE) Polyester
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	355.6 mm 14 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Breaking Strength	566.99 kg 1250 lb
Pull Line Type	Tape
Pulling Tension, maximum	358.338 kg 790 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	251.5 kg/km 169 lb/kft
-------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance	ESCR—Environmental Stress Crack Resistance
---------------------------------------	--