

CT-8-TCPUSE-NI6

8 dB, Tapper, 340–960/1710–2700 MHz



OBSOLETE

This product was discontinued on: October 31, 2019

Replaced By:

CT-8-TUW-NI6

8 dB, Tapper, 340 – 6000 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Tapper

General Specifications

Device Type

Tapper

Application

Indoor/Outdoor

Color

Silver

Inner Contact Plating

Silver

Interface

N Female

Outer Contact Plating

Trimetal

Dimensions

Height

25 mm | 0.984 in

Width

43 mm | 1.693 in

Length

141 mm | 5.551 in

Electrical Specifications

3rd Order IMD

-160 dBc

3rd Order IMD Test Method

Two +43 dBm carriers

CT-8-TCPUSE-NI6

Insertion Loss at Frequency Band	1.1 dB @ 1710–2700 MHz 1.1 dB @ 340–698 MHz 1.1 dB @ 698–960 MHz
Return Loss, minimum	19.1 dB
Average Power, maximum	200 W
Coupling	8 dB
Coupling Tolerance	±0.8dB @ 1710–2700 MHz ±0.8dB @ 698–960 MHz ±1.2dB @ 340–698 MHz
Impedance	50 ohm
Operating Frequency Band	1710 – 2700 MHz 340 – 960 MHz
Peak Power, maximum	3 kW
Reflected Power, maximum	200 W
VSWR	1.25

Mechanical Specifications

Coupling Nut Proof Torque	4.5 N-m 39.828 in lb
----------------------------------	------------------------

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	40 mm 1.575 in
Width, packed	90 mm 3.543 in
Length, packed	180 mm 7.087 in
Volume	648000 mm ³ 39.544 in ³
Weight, gross	0.31 kg 0.683 lb
Weight, net	0.26 kg 0.573 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

CT-8-TCPUSE-NI6

