SWH-200-10



PIM Free, SnapWrap Cable Management Strap. Bundle multiple cable types and sizes into a 1/2" (12.7mm) to 2" (50.8mm) bundle with Snap-in installation. Package of 10

- Manage multiple cables in a single universal wrapping strap
- Replaces hangers and endless combinations of multi-cable grommets

12.7 mm | 0.5 in

- Simpler BOMs, easier standardization
- Optimized to reduce PIM while maximizing structural integrity

Product Classification

Product Type Cable management

Product Brand PIM-Guard

Ordering Note CommScope® standard product (Global)

General Specifications

Accessories Hangers
Color Black

Hanger Type Snap-in hanger

Mounting 3/4 in drilled cable ladder

Patent Number For patents see www.cs-pat.com

Dimensions

Maximum Stack Height 0

 Height
 34.8 mm | 1.37 in

 Width
 34.8 mm | 1.37 in

 Length
 228.6 mm | 9 in

 Compatible Cable Diameter Range
 12.7-50.8 mm

 Compatible Diameter, maximum
 50.8 mm | 2 in

Material Specifications

Compatible Diameter, minimum

Material Type Engineered plastic

Mechanical Specifications



SWH-200-10

Tensile Strength 6,894.76 N/mm² | 1000000 psi

Vibration Survival ≥4 hours at resonant frequency

Wind Speed, survival with 1/2 in (12 mm) radial ice 201.168 km/h | 125 mph

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 5 cm | 1.969 in

 Width, packed
 18 cm | 7.087 in

 Length, packed
 31 cm | 12.205 in

Packaging quantity 10

Weight, gross 0.15 kg | 0.331 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Tensile Strength Tensile Strength at 73° F

