


# 760250711 | TENIO-B6-TRAY-RR



TENIO™ Rollable Ribbon Splice Tray for Small closures (B6 size) for up to 4 Ribbon splice protectors (48 Rollable ribbon fibers) per tray. Max capacity of 6 Rollable Ribbon trays per closure.

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America
<b>Product Type</b>	Fiber splice tray
<b>Product Series</b>	TENIO

## General Specifications

<b>Color</b>	Gray
<b>Splice Tray Chip Type</b>	Heat shrink
<b>Splice Tray Included, quantity</b>	1
<b>Splices per Tray, note</b>	4 x R12 splice protectors

## Dimensions

<b>Height</b>	8 mm   0.315 in
<b>Splice Protector Length, maximum</b>	43 mm   1.693 in
<b>Splice Protector Length, minimum</b>	39 mm   1.535 in
<b>Splice Protector Diameter, maximum</b>	5 mm   0.197 in
<b>Splice Protector Diameter, minimum</b>	3.5 mm   0.138 in

## Material Specifications

<b>Material Type</b>	PBT   PET
----------------------	-----------

## Mechanical Specifications

<b>Minimum Bend Radius, standard</b>	30 mm   1.181 in
--------------------------------------	------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
------------------------------	--------------------------------------

# 760250711 | TENIO-B6-TRAY-RR

---

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Environmental Space** Outdoor

## Packaging and Weights

**Packaging quantity** 6

**Packaging Type** Bag | Carton

**Weight, net** 0.1 kg | 0.22 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

